








REV.	ECN NO.	DESCRIPTION	DATE	DESIGN



PIN number variable size comparison table			
PART NO	PIN	A	B
JXT-HA2.54-2PWZ	2	2.50	7.50
JXT-HA2.54-3PWZ	3	5.00	10.00
JXT-HA2.54-4PWZ	4	7.50	12.50
JXT-HA2.54-5PWZ	5	10.00	15.00
JXT-HA2.54-6PWZ	6	12.50	17.50
.....			
JXT-HA2.54-20PWZ	20	47.50	52.50

技术要求:

1. 塑件材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 $235\pm 5^{\circ}$, 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求。

2	端子 Contact	黄铜	N*1	电镀(锡): 整个表面镀底镍 30u"MIN, 再镀锡80u"MIN
1	基座 Wafer	PA66 (UL94V-0)	1	白色
序号	名称	材料	数量	备注

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.° ±5°	PART NO.	TITLE:		
.XX±0.20	X.X° ±1°	JXT-HA2.54-NPWZ	HA2.54MM 带扣 弯针		
.XXX±0.10	X.XX°±0.5°	DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	— — —	APPD: Ava		N:A	1/1
FINISH	— — —				