

TOLL Plastic-Encapsulate MOSFETS

Features

- VDS=85V
- ID=160A
- RDS(on)@VGS=10V < 4.6mΩ
- Low Gate Charge and Rdson
- Fast Switching Speedze
- Advanced Split Gate Trench Technology

Drain-source Voltage
85 V
Drain Current
160 Ampere



Applications

- Power switching application
- DC-DC Converter
- Power Management

Mechanical Data

- Case: TOLL
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant,halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Ordering Information

Table with 7 columns: PACKAGE, PACKAGE CODE, UNIT WEIGHT(g), REEL(pcs), BOX(pcs), CARTON(pcs), DELIVERY MODE. Row 1: TOLL, R3, 0.753, 2000, 4000, 28000, 13"

Maximum Ratings (Ta=25°C Unless otherwise specified)

Table with 4 columns: PARAMETER, SYMBOL, UNIT, VALUE. Rows include: Drain-source Voltage (VDS, V, 85), Gate-source Voltage (VGS, V, ±20), Drain Current (ID, A, 160), Pulsed Drain Current (IDM, A, 640), Total Power Dissipation (PD, W, 246), Single pulse avalanche energy (EAS, mJ, 324), Junction temperature (TJ, °C, -55 ~+150), Storage temperature (Tstg, °C, -55 ~+150), Thermal Resistance Junction-to-Case (RθJC, °C / W, 0.51).

● Static Parameter Characteristics (Tj=25°C Unless otherwise specified)

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} = 0V, I _D =250μA	V	85	—	—
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =85V, V _{GS} =0V	μA	—	—	1.0
Gate-Body Leakage Current	I _{GSS}	V _{GS} = ±20V, V _{DS} =0V	nA	—	—	±100
Gate Threshold Voltage	V _{GS(th)}	V _{DS} = V _{GS} , I _D =250μA	V	2	3	4
Static Drain-Source On-Resistance ⁽³⁾	R _{DS(ON)}	V _{GS} = 10V, I _D =50A	mΩ	—	3.8	4.6

● Dynamic Parameters

PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Input Capacitance	C _{iss}	V _{DS} =40V, V _{GS} =0V, f=1MHZ	pF	—	3457	—
Output Capacitance	C _{oss}			—	740	—
Reverse Transfer Capacitance	C _{rss}			—	25	—

● Switching Parameters







PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Turn-on Delay Time	t _{D(on)}	V _{GS} =10V, V _{DD} =40V, I _D =50A ,R _{GEN} =3Ω	nS	—	17	—
Turn-on Rise Time	t _r		nS	—	39	—
Turn-off Delay Time	t _{D(off)}		nS	—	64	—
Turn-off fall Time	t _f		nS	—	42	—
Total Gate Charge	Q _g	V _{DS} =40V, I _D =50A V _{GS} =10V	nC	—	56	—
Gate-Source Charge	Q _{gs}		nC	—	18.2	—
Gate-Drain Charge	Q _{gd}		nC	—	15	—

● Drian-Source Diode Characteristics






PARAMETER	SYMBOL	Condition	UNIT	Min	Typ	Max
Diode Forward Voltage	V _{SD}	I _S =160A, V _{GS} =0V	V	—	—	1.2
Maximum Body-Diode Continuous Current	I _S	—	A	—	—	160
Reverse Recovery Time	T _{rr}	I _S =160A, di/dt=100A/us, TJ=25°C	nS	—	45	—
Reverse Recovery Charge	Q _{rr}		nC	—	56	—

Note :
(1)Repetitive Rating: Pulse width limited by maximum junction temperature.
(2)EAS condition : Tj=25°C ,VDD=40V,VG=10V,L=0.5mH,IAS=36A,Rg=25Ω.
(3)Pulse Test: Pulse Width ≤ 300μs, Duty Cycle ≤ 2%.


● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)





● Package Outline Dimensions (TOLL)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	2.20	2.4	0.087	0.094
b	0.65	0.90	0.026	0.035
b1	9.7	9.90	0.382	0.390
b3	1.15	1.35	0.045	0.053
c	0.40	0.60	0.016	0.024
D	10.28	10.48	0.405	0.413
D2	3.20	3.40	0.126	0.134
D4	4.45	4.65	0.175	0.183
E	9.80	10.00	0.386	0.394
E1	7.90	8.30	0.311	0.327
E2	2.8	3.20	0.110	0.126
e	1.2BSC		1.2BSC	
H	11.48	11.88	0.452	0.468
H1	6.95REF		6.95REF	
j	0.35REF		0.35REF	
K	3.0REF		3.0REF	
L	1.35	1.75	0.053	0.069
L1	0.50	0.90	0.020	0.035
L2	0.50	0.70	0.020	0.028
L3	0.25	0.65	0.010	0.026
Q	8.0REF		8.0REF	
θ	10° REF		10° REF	



● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	9.95	10.2	0.392	0.402
A1	2.60	2.80	0.102	0.110
B	8.2	8.3	0.323	0.327
b	0.6	0.8	0.024	0.031
C	0.9	1.1	0.035	0.043
c	0.6	0.8	0.024	0.031
D	6.7	6.9	0.264	0.272
D1	13.1	13.3	0.516	0.524
e	1.0	1.2	0.039	0.047
e1	0.2	0.4	0.008	0.016



1. Gate Charge Test Circuit & Waveforms



2. Resistive Switching Test Circuit & Waveforms



3. Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



4. Diode Recovery Test Circuit & Waveforms

