






REV.	ECN.NO.	MODIFY.CONTENT	DATE
A		NEW	2015/11/29



Specification:

*Electrical Characteristics:

Contact Current Rating:1.0 Amperes
Dielectric Withstanding Voltage:AC500V r.m.s
Insulation Resistance:500ΩM Minimum
Contact Resistance:30Ωm Maximum

*Environmental:

OPerating Temperature:-55°C~+85°C
Mating Cycles:5000 Insertions

*Material:

Insulator:HI-Temp Plastic UL94v-0 Rated
Contact:Copper Alloy
Shell:SUS

TYPE	"A"	Part NO
H=1.80mm	1.80mm	5001B-SIM180-103
H=1.50mm	1.50mm	5001B-SIM150-102

GENERAL TOLERANCE			DWG NO.		APPD:	WIND	Scale	1:1
X.±0.45		x.°±5°	Title	SIM CARD 6PIN 连桥带档 (防溃PIN)	CHKD:		UNIT	mm
.X±0.35		.x.°±2°			DR:			
.XX±0.25		.xx.°±1°	Part NO.	5001B-SIM180-103	Date	2015/11/29		
.XXX±0.15		.xxx.°±0.5°			东莞市文章济美电子有限公司			
SHEET	1/1							