






SUGGESTED PCB LAYOUT
(COMPONENT SIDE)

技术要求:

1. 塑件材料: PA66 (UL-94V-0)
2. 接触件: 黄铜镀锡
3. 接触电阻: $\leq 10m\Omega$
4. 绝缘电阻: $\geq 100M\Omega$
5. 额定电压: 250V AC DC
6. 额定电流: 2.0A AC DC
7. 耐压: 能承受 1000V AC/Minute
8. 工作温度: $-25^{\circ}\sim+85^{\circ}$
9. 可焊性试验: 浸锡面积 $\geq 95\%$ 温度 235^{+5}_{-0} , 时间 2.5 ± 0.5 秒
10. 铅和镉等六大有害物质含量要符合环保要求.



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PIN number variable size comparison table

PART NO	PIN	A	B	C
JXT-HY2.0-2PWZ	2	2.00	6.00	2.50
JXT-HY2.0-3PWZ	3	4.00	8.00	2.50
JXT-HY2.0-4PWZ	4	6.00	10.00	3.50
JXT-HY2.0-5PWZ	5	8.00	12.00	5.50
JXT-HY2.0-6PWZ	6	10.00	14.00	7.50
JXT-HY2.0-7PWZ	7	12.00	16.00	9.50
JXT-HY2.0-8PWZ	8	14.00	18.00	11.50
.....				
JXT-HY2.0-15PWZ	15	28.00	32.00	15.50

2	端子 Contact	黄铜	N*1	电镀(锡):整个表面镀底镍 30u"MIN,再镀锡 80u"MIN	
1	基座 Wafer	PA66 (UL94V-0)	1	白色	
序号	名称	材料	数量	备注	
TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
.X±0.30	X.* ±5°	PART NO.		TITLE:	
.XX±0.20	X.X* ±1°	JXT-HY2.0-NPWZ		HY2.0MM 弯针带扣	
.XXX±0.10	X.XX* ±0.5°	DESIGN: Ethan		MANUFACTURE DWG	
UNITS	mm	CHED: Olvia			
MATERILA	— — —	APPD: Ava			
FINISH	— — —			SCALE	SHEET
				N:A	1/1