





P/N	PIN	DIM.A	DIM.B
PM2.00-2-01P-Z	2*1	0.00	2.00
PM2.00-2-02P-Z	2*2	2.00	4.00
PM2.00-2-03P-Z	2*3	4.00	6.00
PM2.00-2-04P-Z	2*4	6.00	8.00
PM2.00-2-05P-Z	2*5	8.00	10.00
PM2.00-2-06P-Z	2*6	10.00	12.00
PM2.00-2-07P-Z	2*7	12.00	14.00
PM2.00-2-08P-Z	2*8	14.00	16.00
PM2.00-2-09P-Z	2*9	16.00	18.00
.....			
PM2.00-2-40P-Z	2*40	(PIN-1)x2.0	(PIN)x2.0

SPECIFICATIONS

Current Rating: 1.5 Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20m Ω Max
Withstanding Voltage: AC 500V
Operation Temperature: -40 $^{\circ}$ to+105 $^{\circ}$
Contact Material: Brass
Standard: PA6T
Insulator Material: Polyester(UL 94V-0)
Contact Plating: Gold Flash
Max.Processing Temp: 240 $^{\circ}$ C for30-60seconds
(260 $^{\circ}$ C for 5 seconds)



RECOMMEND P.C.B LAYOUT
PCB TOLERANCE:±0.05 (TOP VIEW)

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.3	X.*± 5°	APR.	Alex	TITLE: 2.0FH H6.35 2xnPin 180 μ Y μ PC2.8 6T	
.XX±0.2	.X*± 1	CHK.	Jack	DWG NO. PM2.00-2-NP-S	
.XXX±0.1	.XX*± 0.5	DRA.	Can	PROJ. 	CUSTOMER DRAWING
				SIZE A4	SCALE 1:1