

SOT-523 Plastic-Encapsulate Transistors



Features

- Complimentary to 2SA1774
- Power dissipation of 150mW

Mechanical Data

- Case: SOT-523
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

Function Diagram



Collector-Emitter Voltage
V_{CEO} 50V
Collector Current
0.15 Ampere



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-523	R1	0.0025	3000	15000	150000	7"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Collector-Base Voltage	V _{CBO}	V	60
Collector-Emitter Voltage	V _{CEO}		50
Emitter-Base Voltage	V _{EBO}		7
Collector Current	I _C	A	0.15
Collector Power Dissipation	P _C	mW	150
Storage temperature	T _{stg}	°C	-55 ~+150
Junction temperature	T _j	°C	-55 ~+150

● Electrical Characteristics (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Type	Max
Collector-Base Breakdown Voltage	$V_{(BR)CBO}$	V	$I_C=50\mu A, I_E=0$	60	—	—
Collector-Emitter Breakdown Voltage	$V_{(BR)CEO}$		$I_C=1\mu A, I_B=0$	50	—	—
Emitter-Base Breakdown Voltage	$V_{(BR)EBO}$		$I_E=50\mu A, I_C=0$	7	—	—
Collector cut-off current	I_{CBO}	nA	$V_{CB}=60V, I_E=0$	—	—	100
Emitter-Base cut-off current	I_{EBO}		$V_{EB}=7V, I_C=0$	—	—	100
DC current gain	h_{FE}		$I_C=1mA, V_{CE}=6V$	120	—	560
Collector-Emitter Saturation Voltage	$V_{CE(sat)}$	V	$I_C=50mA, I_B=5mA$	—	—	0.5
Collector output capacitance	C_{ob}	pF	$V_{CB}=12V, I_E=0, f=1MHz$	—	2.0	3.5







● CLASSIFICATION OF h_{FE}

ITEM	R
h_{FE}	180-390

● Small-signal Characteristics

ITEM	SYMBOL	Condition	UNIT	Min	TYP	Max
Transition frequency	f_T	$I_E=2mA, V_{CE}=12V, f=30MHz$	MHz	—	180	—

● Ratings And Characteristics Curves (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (SOT-523)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.65	0.85	0.026	0.033
A1	0.40	0.60	0.016	0.024
B	0.25	0.35	0.010	0.014
b	0.15	0.25	0.006	0.010
C	0.05	0.15	0.002	0.006
D	0.70	0.90	0.028	0.035
D1	1.50	1.70	0.059	0.067
E	1.5	1.7	0.059	0.067
e	0.95	1.05	0.037	0.041
H	-	0.10	-	0.004
L	0.17	-	0.007	-

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.50	0.70	0.020	0.028
B	0.60	0.80	0.024	0.031
C	0.90	1.10	0.035	0.043
D	1.20	1.40	0.047	0.055