

1.Features

- $V_{DSS} = -30V$
- $R_{DS(ON)} < 11.6m\Omega (V_{GS} = -10V)$
- $R_{DS(ON)} < 18m\Omega (V_{GS} = -4.5V)$
- RoHS Compliant
- High performance trench technology
- for extremely low $R_{DS(ON)}$


2.Applications

- Inverter
- Power Supplies

3.Pinning information

Pin	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE

TO-252(DPAK)
top view



4.Absolute Maximum Ratings $T_A = 25^\circ C$

Parameter		Symbol	Rating	Units
Drain-Source Voltage		V_{DSS}	-30	V
Drain-Source Avalanche Voltage (maximum) (Note 4)		$V_{DS(Avalanche)}$	-40	
Gate-Source Voltage		V_{GSS}	± 25	
Continuous Drain Current	@ $T_C = 25^\circ C$ (Note 3)	I_D	-55	A
	@ $T_A = 25^\circ C$ (Note 1a)		-13	
	Pulsed (Note 1a)		-100	
Power Dissipation	@ $T_C = 25^\circ C$ (Note 3)	P_D	57	W
	@ $T_A = 25^\circ C$ (Note 1a)		3.1	
	@ $T_A = 25^\circ C$ (Note 1b)		1.3	
Operating and Storage Junction Temperature Range		T_J, T_{STG}	-55 to 150	$^\circ C$



5. Thermal Characteristics

Parameter	Symbol	Rating	Units
Thermal Resistance, Junction-to-Case (Note 1)	$R_{\theta JC}$	2.2	$^{\circ}C/W$
Thermal Resistance, Junction-to-Ambient (Note 1a)	$R_{\theta JA}$	40	$^{\circ}C/W$
Thermal Resistance, Junction-to-Ambient (Note 1b)	$R_{\theta JA}$	96	$^{\circ}C/W$



6. Electrical Characteristic (T_J=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min	Typ	Max	Units
Drain-Source Avalanche Energy (Single Pulse)	E _{AS}	V _{DD} =-35V, I _D =-11A, L=1mH		61		mJ
Drain-Source Avalanche Current	I _{AS}			-14		A
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V, I _D =-250μA	-30			V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =-28V, V _{GS} =0V			-1	μA
Gate-Body Leakage	I _{GSS}	V _{GS} =±25V, V _{DS} =0V			±100	nA
Gate Threshold Voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =-250μA	-1	1.6	-3	V
Static Drain-Source On-Resistance	R _{DS(ON)}	V _{GS} =-10V, I _D =-14A		9.7	11.6	mΩ
		V _{GS} =-4.5V, I _D =-11A		14.4	18	mΩ
Forward Transconductance	g _{FS}	V _{DS} =-5V, I _D =-14A		35		S
Input Capacitance	C _{iss}	V _{DS} =-20V, V _{GS} =0V f=1MHz		2370		pF
Output Capacitance	C _{oss}			470		pF
Reverse Transfer Capacitance	C _{rss}			250		pF
Gate Resistance	R _g	f=1MHz		3.6		Ω
Turn-On Delay Time	t _{D(on)}	V _{DD} =-20V, I _D =-1A V _{GS} =-10V, R _{GEN} =6Ω		18	32	ns
Turn-On Rise Time	t _r			10	20	ns
Turn-Off Delay Time	t _{D(off)}			62	100	ns
Turn-Off Fall Time	t _f			36	58	ns
Total Gate Charge, V _{GS} = -10V	Q _g				45	63
Total Gate Charge, V _{GS} = -5V	Q _g	V _{DS} =-20V, I _D =-14A		25	35	nC
Gate-Source Charge	Q _{gs}			7		nC
Gate-Drain Charge	Q _{gd}			10		nC
Drain-Source Diode Forward Voltage	V _{SD}		V _{GS} =0V, I _S =-14A (Note 2)	-0.8	-1.2	
Diode Reverse Recovery Time	t _{rr}	I _F =-14A, di/dt=100A/μs		28		ns
Diode Reverse Recovery Charge	Q _{rr}				15	



Notes:

1. $R_{\theta JA}$ is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins.

$R_{\theta JC}$ is guaranteed by design while $R_{\theta CA}$ is determined by the user's board design.



■ a) $R_{\theta JA}=40^{\circ}\text{C/W}$ when mounted
 ■ on a 1in^2 pad of 2oz copper.



■ b) $R_{\theta JA}=96^{\circ}\text{C/W}$ when mounted
 ■ on a minimum pad.

Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width < 300 μs , Duty Cycle < 2.0%


3. Maximum current is calculated as: $\sqrt{\frac{P_D}{R_{DS(ON)}}}$

where P_D is maximum power dissipation at $T_C=25^{\circ}\text{C}$ and $R_{DS(ON)}$ is at $T_{J(max)}$ and $V_{GS}=10\text{V}$. Package current limitation is 21A

4. $BV_{(avalanche)}$ Single-Pulse rating is guaranteed if device is operated within the UIS SOA boundary of the device.



7.1 Typical characteristic






7.2 Typical characteristic

<p style="text-align: center;">Q_g, Gate Charge (nC)</p>	<p style="text-align: center;">V_{DS}, Drain To Source Voltage (V)</p>
<p style="text-align: center;">Figure 7: Gate Charge Characteristics</p>	<p style="text-align: center;">Figure 8: Capacitance vs Drain to Source Voltage</p>
<p style="text-align: center;">$-V_{DS}$, Drain To Source Voltage (V)</p>	<p style="text-align: center;">t_1, TIME (sec)</p>
<p style="text-align: center;">Figure 9: Maximum Safe Operating Area</p>	<p style="text-align: center;">Figure 10: Single Pulse Maximum Power Dissipation</p>
<p style="text-align: center;">t_1, TIME (sec)</p>	<p style="text-align: center;">t_{AV}, Time In Avanche(ms)</p>
<p style="text-align: center;">Figure 11: Single Pulse Maximum Peak Current</p>	<p style="text-align: center;">Figure 12: Unclamped Inductive Switching Capability</p>



7.3 Typical characteristic





8. Test Circuits and Waveforms




Figure 14. Unclamped Inductive Load Test Circuit




Figure 15. Unclamped Inductive Waveforms




Figure 16. Gate Charge Test Circuit




Figure 17. Gate Charge Waveform




Figure 18. Switching Time Test Circuit





Figure 19. Switching Time Waveforms



9.TO-252 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

Symbol	A	A1	A2	B	B1	B2	B3	B4	B5	B6	C	D
Min	5.1	6.4	5.6	9.5	5.9	1.35	0.4	0.1	0.85	4.35	2.15	2.286
Max	5.5	6.8	6.0	10.3	6.3	1.65	0.6	(typ.)	1.05	4.65	2.45	(typ.)

Symbol	D1	D2	D3	D4	D5	E	E1	R	R1	R2	R3
Min	0.66	0.81	0.65	0.42	0.42	0.86	0.05	0°	7°	7°	7°
Max	0.86	1.01	0.95	0.58	0.58	1.16	0.05	6°	(typ.)	(typ.)	(typ.)



10. Ordering information



yy: Year Code
ww: Week Code

Order Code	Package	Base QTY	Delivery Mode
UMW FDD6637	TO-252	2500	Tape and reel



11.Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.