






技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电流: 0.5A
4. 额定电压: 50V, AC.
5. 接触电阻: $\leq 50\text{m}\Omega$ MAX.
6. 绝缘电阻: $\geq 500\text{M}\Omega$ Min.
7. 耐电压: 150V AC/1Minute



P/N	PIN	DIM A	DIM B	DIM C	DIM D	DIM E	DIM F
BX-FC05-FLK-H54-5P	5	2.00	3.06	6.00	4.40	2.50	4.00
BX-FC05-FLK-H54-6P	6	2.50	3.56	6.50	4.90	3.00	4.50
BX-FC05-FLK-H54-7P	7	3.00	4.06	7.00	5.40	3.00	5.00
BX-FC05-FLK-H54-8P	8	3.50	4.56	7.50	5.90	4.00	5.50
BX-FC05-FLK-H54-9P	9	4.00	5.06	8.00	6.40	4.00	6.00
BX-FC05-FLK-H54-10P	10	4.50	5.56	8.50	6.90	4.00	6.50
BX-FC05-FLK-H54-11P	11	5.00	6.06	9.00	7.40	4.00	7.00
BX-FC05-FLK-H54-12P	12	5.50	6.56	9.50	7.90	4.00	7.50
BX-FC05-FLK-H54-13P	13	6.00	7.06	10.00	8.40	4.00	8.00
BX-FC05-FLK-H54-14P	14	6.50	7.56	10.50	8.90	4.00	8.50
BX-FC05-FLK-H54-15P	15	7.00	8.06	11.00	9.40	4.00	9.00
BX-FC05-FLK-H54-16P	16	7.50	8.56	11.50	9.90	4.00	9.50
.....							
BX-FC05-FLK-H54-56P	56	27.50	28.56	31.50	29.90	8.00	29.50
BX-FC05-FLK-H54-57P	57	28.00	29.06	32.00	30.40	8.00	30.00
BX-FC05-FLK-H54-58P	58	28.50	29.56	32.50	30.90	8.00	30.50
BX-FC05-FLK-H54-59P	59	29.00	30.06	33.00	31.40	8.00	31.00
BX-FC05-FLK-H54-60P	60	29.50	30.56	33.50	31.90	8.00	31.50

序号	品名	材质	制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	EMMA		料号 PART NO.	BX-FC05-FLK-H54-NP	版本 REV.	A
1	0.5 Pitch 立式胶芯 (H=5.4)	LCP UL94V-0 本色				X.±0.50	±1°	审核 CHECK	EVA		品名 TITLE	0.5 Pitch 立式胶芯 (H=5.4) 业务图	页次 SHEET	1/1
2	0.5 Pitch 立式后盖 (H=5.4)	LCP UL94V-0 黑色				.X±0.20		核准 APPROVAL	JADE		客户料号 CUTM.NO.			
3	0.5 Pitch 立式端子 (H=5.4)	铜合金/表面镀金				.XX±0.10		单位 UNITS	MM	比例 SCALE	1:1			
4	0.5 Pitch 立式焊片 (H=5.4)	铜合金/表面镀锡												