










PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11	—	B2	—
A10	—	B3	—
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3	—	B10	—
A2	—	B11	—
A1	GND	B12	GND



RECOMMENDED P.C.B. LAYOUT (T:0.8mm)
TOLERANCE UNSPECIFIED ±0.05mm

NO.	PART NAME	Q'TY	MATERIAL	FINISH
5	CAP	1	High temperature plastic	UL94 V-0,Black
4	Shell	1	Stainless Steel,T=0.30mm	30u"Ni Min.
3	GroundBar	1	Stainless Steel,T=0.15mm	No Plating
2	Contact	16	Copper Alloy,T=0.15mm	Au/Ni-Plated
1	Housing	1	High temperature plastic	UL94 V-0,Black

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-TYPE-C-423	版本 REV.	A
			X.:±0.50	X.:±5°	审核 CHECK	LEO			品名 TITLE	TYPE-C 16p 引脚间距H10.0mm	页次 SHEET	1/1
			X.X:±0.35	X.X:±3°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.			
			X.XX:±0.25	X.XX:±2.5°	单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.			




说明:

1. 每卷前后各空10PCS,尾部用美纹胶纸封住;
2. 将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
3. 每10卷盘一叠共2500Pcs并装入1个外箱内;
4. 在搬运过程中要轻拿轻放;
5. 在运输中不可堆放过多(1.8M最高),不可重压;
6. 跌落测试条件:

成品箱从1.2米高度自由落体(一角三棱六面):

- a. 产品不可跑出下带凹槽;
- b. 产品不可有摔伤,变形;
- c. 内包装材料不可严重破损.

NO.	NAME	SPEC	Q'TY
0	TYPE C RECEPTACLE		2500PCS/CARTON
1	CARRIER TAPE	W=24mm,T=0.50mm	250PCS/PLATE
2	COVER TAPE	W=21.3mm	10PLATES/CARTON
3	REEL PLATE	ø330*100*24.4mm	10PCS/CARTON
4	RoHS LABEL		10PCS/CARTON
5	PRODUCT LABER		10PCS/CARTON
6	CARTON	350*340*310mm	1PCS/PACKAGE

制图 DRAWN	变更内容 DESCRIPTION	日期 DATE	GENERAL TOLERANCE		制图 DRAWING	ROSE			料号 PART NO.	ZX-TYPE-C-423		版本 REV.	A
			X.:±0.50	X.:±5°	审核 CHECK	LEO			品名 TITLE	TYPE-C 16p 引脚间距H10.0mm		页次 SHEET	1/1
			X.X:±0.35	X.X:±3°	核准 APPROVAL	JOHN			客户料号 CUTM.NO.				
			X.XX:±0.25	X.XX:±2.5°									
					单位 UNITS	MM	比例 SCALE	1:1	 兆星精密电子（深圳）有限公司 ShenZhen ZhaoXing Precision electronics Co., Ltd.				