



[illegible]


—BODY
MATERIAL : CuNiSi F57
SURFACE : SEE CHART



- 1 DATE-CODE (WEEK/YEAR (E.G. WEEK NUMBER 30/ YEAR 2011)) 
AND TE REVISION (E.G. REV. A)
- 2 DETAILS OF DESIGN ARE LEFT TO MANUFACTURER
- 3 WITH DOUBLE OUT DIES THE FIRST SPRING WILL BE PROVIDED
WITH AN INDICATION "-"



A3



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.ZHANG	10NOV2022	 TE Connectivity					
		CHK J.GU	10NOV2022						
DIMENSIONS: mm		APVD W.ZHANG	10NOV2022	NAME MQS CLEAN BODY Productgroup Drawing Socket Contact					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ± ± ± ± ± ±0.2 ANGLES ± 1°	PRODUCT SPEC 108-18030							
		APPLICATION SPEC 114-18021							
		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO				
		A2	00779	©=2435194	-				
MATERIAL		WEIGHT							
		-		CUSTOMER DRAWING					
				SCALE	10:1	SHEET	1 OF 1	REV	A3