





G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- 2.Withstanding voltage: 24V AC
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles


USB IF TID:12014

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First


B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First



PCB REFERENCE DIAGRAM
TOLERANCE:±0.05



NO.	PARTS	MATERIAL	REMARKS
1	SHELL	STAINLESS STEEL304	Ni 30u" Min PLATED
2	MID PLATE	STAINLESS STEEL301	Ni 30u" Min PLATED
3	HOUSING	LCP	BLACK UL 94 V-0
4	TERMINALS	COPPER ALLOY C1815	Au1u" PLATED ON CONTACT AREA G/F PLATED ON SOLDER AREA



RoHS
Compliant
EU RoHS Standards



SCALE: 1:1 UNIT: mm
SIZE: A4

Unless otherwise
General Tolerance:
X. ±0.40
X.x ±0.30
X.xx ±0.20
X.xxx ±0.10
X° ±5°

Title: Vertical Type-C 16P Female
SMT H=6.8mm

Molde Code: GT-USB-9055CA

DRAWN	CHECKED	APPROVED	DATE
Wu	Chen	Chen	2026.01.08

品赞科技
b-Switch
www.dg-switch.com

REV: A0 SHEET: 1/1