

DFN1610-2L Plastic-Encapsulate ESD Protection Diodes


Features

- Low leakage current
- Low clamping voltage
- IEC 61000-4-2 (ESD Air): $\pm 30\text{kV}$
- IEC 61000-4-2 (ESD Contact): $\pm 30\text{kV}$
- IEC 61000-4-5 (Lightning 8/20 μs): 120A

Applications

- Mobile Phone, Digital cameras
- Battery Protection
- Power Line Protection
- Vbat pin for Mobile Devices
- Hand Held Portable Applications

Function Diagram



Reverse Working Voltage
7.0 V Max.
High Capacitance
600 pF (Typ).




Maximum Ratings (Ta=25°C Unless otherwise specified)

SYMBOL	PARAMETER	CONDITIONS	VALUE	UNIT
V _{ESD}	Electrostatic Discharge Voltage	ESD per IEC 61000-4-2(Air)	± 30	KV
		ESD per IEC 61000-4-2(Contact)	± 30	KV
P _{PP}	Peak Pulse Power	tp = 8/20 μs	2400	W
I _{PP}	Rated Peak Pulse Current	tp = 8/20 μs	120	A
T _J	Operating JunctionTemperature Range	—	-55 to +125	°C
T _{STG}	Operating JunctionTemperature Range	—	-55 to +125	°C

Electrical Parameter





SYMBOL	PARAMETER
V _C	Clamping Voltage @ I _{PP}
V _{BR}	Breakdown Voltage @ I _T
I _{PP}	Peak Pulse Current
I _T	Test Current
I _R	Reverse Leakage Current @ VRWM
V _{RWM}	Peak Reverse Working Voltage
P _{PP}	Peak Pulse Power Dissipation
C _J	Junction Capacitance @ V _R =0V,f=1MHz
I _F	Forward Current
V _F	Forward Voltage @I _F



● **Electrical Characteristics** (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	CONDITION	Min	Typ	Max	UNIT
Peak Reverse Working Voltage	V_{RWM}	$T_a=25^\circ\text{C}$	—	—	7.0	V
Breakdown Voltage	V_{BR}	$I_T=1.0\text{mA}, T_a=25^\circ\text{C}$	7.6	—	—	V
Reverse Leakage Current	I_R	$V_{RWM}=7.0\text{V}, T_a=25^\circ\text{C}$	—	0.1	0.5	μA
Clamping Voltage	V_C	$I_{PP}=120\text{A}, t_p=8/20\mu\text{s}$	—	20	—	V
Junction Capacitance	C_J	$V_{RWM}=0\text{V}, f=1\text{MHz}$	—	600	—	pF


● **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)



Ordering Information


PREFERRED P/N	PACKAGE	SIZE(mm)	DELIVERY MODE	MPQ(PCS)
H7VH16UA	DFN1610-2L	1.575×0.975×0.485	7" REEL	3000

Recommended Soldering Conditions




Profile Feature		Pb-Free Assembly
Pre-heat	Temperature Min ($T_{S(min)}$)	+150°C
	Temperature Max ($T_{S(max)}$)	+200°C
	Time (Min to Max) (t_s)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{S(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	Temperature (T_L) (Liquid us)	+217°C
	Temperature (t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		20-40secs
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C

Package Outline Dimensions (DFN1610-2L)



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.46	0.56	0.018	0.022
A1	0.01	0.05	0.001	0.003
b	0.75	0.85	0.030	0.033
b1	0.25	0.35	0.010	0.014
D	1.55	1.65	0.061	0.065
E	0.95	1.05	0.037	0.041
e	1.10BSC		0.043 BSC	
L	0.35	0.45	0.014	0.018
A3	0.127REF		0.005REF	

Suggested Pad Layout



Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
X	0.57	0.67	0.024	0.028
Y	0.95	1.05	0.039	0.043
L	1.79	1.89	0.072	0.076
e	1.17	1.27	0.048	0.052
K	0.55	0.65	0.024	0.028