





REV	ECN No.	DESCRIPTION	DATE
A	EC-20100801	标准化	2020.10.08




芯数	A	B	C
2	2.0	8.0	4.8
3	4.0	10.0	6.8
4	6.0	12.0	8.8
5	8.0	14.0	10.8
6	10.0	16.0	12.8
7	12.0	18.0	14.8
8	14.0	20.0	16.8
9	16.0	22.0	18.8
10	18.0	24.0	20.8
11	20.0	26.0	22.8
12	22.0	28.0	24.8
13	24.0	30.0	26.8
14	26.0	32.0	28.8
15	28.0	34.0	30.8
16	30.0	36.0	32.8



PCB LAYOUT
TOL.: ±0.05

说明:

1. 产品表面清洁, 无锈蚀、氧化、裂纹、缺芯、毛刺、及其它机械损伤;
2. 塑胶材料: 耐高温树脂, 颜色: 本色;
3. 接触针材料: 黄铜, 镀锡;
4. 焊片材料: 磷青铜, 镀锡;



序号	名称	数量
1	基座	1
2	阳接触针	n
3	焊片	2

东莞市高钺达电子科技有限公司				NAME(INTENDED USE)			
APPROVALS		DATE		TOLERANCES UNLESS OTHERWISE SPECIFIED		PART NO.:	
DR:		2020.10.08		X.±0.30		X.±5°	
CHKD:				.X±0.25		.X±3°	
APPD:		2020.10.08		.XX±0.20		.XX±1°	
						DRAWING NO.:	
						7700-XXK3-TG	
				SIZE		UNITS	
				A4		mm	
				SCALE		SHEET	
				1:1		1/1	