


-30V P-CHANNEL ENHANCEMENT MODE MOSFET

MAIN CHARACTERISTICS

I_D	-30A
V_{DSS}	-30V
R_{DS(on)-typ}(@V_{GS}=-10V)	< 20mΩ (Typ:16 mΩ)
R_{DS(on)-typ}(@V_{GS}=-4.5V)	< 30mΩ (Typ:23 mΩ)



Application

- ♣ Lithium battery protection
- ♣ Wireless impact
- ♣ Mobile phone fast charging

Maximum Ratings at T_c=25°C unless otherwise specified

Characteristics	Symbols	Value	Units
Drain-Source Voltage	V_{DS}	-30	V
Gate - Source Voltage	V_{GS}	±20	V
Continuous Drain Current, V _{GS} @ -10V ¹ @T _c =25°C	I_D	-30	A
Continuous Drain Current, V _{GS} @ -10V ¹ @T _c =100°C	I_D	-22	A
Pulsed Drain Current ²	I_{DM}	-70	A
Single Pulse Avalanche Energy ³	E_{AS}	72.2	mJ
Avalanche Current	I_{AS}	-38	A
Total Power Dissipation ⁴ @T _c =25°C	P_D	34.7	W
Storage Temperature Range	T_{STG}	-55 to +150	°C
Operating Junction Temperature Range	T_J	-55 to +150	°C
Thermal Resistance Junction-Ambient	R_{θJA}	62.5	°C/W
Thermal Resistance Junction-Case ¹	R_{θJC}	3.6	°C/W

Maximum Ratings at Tc=25°C unless otherwise specified

Characteristics	Test Condition	Symbols	Min	Typ	Max	Units
Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=-250\mu A$	BV_{DSS}	-30	-33	-	V
Zero Gate Voltage Drain Current	$V_{DS}=-30V, V_{GS}=0V$	I_{DSS}	-	-	-1	μA
Gate –Source Leakage Current	$V_{GS}=\pm 20V, V_{DS}=0V$	I_{GSS}	-	-	± 100	nA
Gate Threshold Voltage	$V_{DS}=V_{GS}, I_D=-250\mu A$	$V_{GS(th)}$	-1.0	-1.5	-2.5	V
Static Drain-Source On-Resistance ³	$V_{GS}=-10V, I_D=-10A$	$R_{DS(on)}$	-	16	20	m Ω
	$V_{GS}=-4.5V, I_D=-5A$		-	23	30	
Input Capacitance	$V_{DS}=-15V$ $V_{GS}=0V$ $f=1.0MHz$	C_{iss}	-	1550	-	μF
Output Capacitance		C_{oss}	-	327	-	
Reverse Transfer Capacitance		C_{rss}	-	278	-	
Total Gate Charge	$V_{DS}=-15V$ $V_{GS}=-10V$ $I_D=-9.1A$	Q_g	-	30	-	nC
Gate-Source Charge		Q_{gs}	-	5.3	-	
Gate-Drain(“Miller”) Charge		Q_{gd}	-	7.6	-	
Turn-on delay time	$V_{DD}=-15V,$ $I_D=-6A$ $V_{GS}=-10V$ $R_{GEN}=2.5\Omega$	$t_{d(on)}$	-	14	-	ns
Rise Time		T_r	-	20	-	
Turn-Off Delay Time		$t_{d(OFF)}$	-	95	-	
Fall Time		t_f	-	65	-	
Maximum Continuous Drain to Source Diode Forward Current		I_S	-	-	-30	A
Maximum Pulsed Drain to Source Diode Forward Current		I_{SM}	-	-	-70	A
Drain to Source Diode Forward Voltage	$V_{GS}=0V, I_S=-11A$	V_{SD}	-	-0.8	-1.2	V

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\cong 300\mu s$, duty cycle $\cong 2\%$
- 3.The EAS data shows Max. rating . The test condition is $V_{DD}=-25V, V_{GS}=-10V, L=0.1mH, I_{AS}=-5A$
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as ID and IDM , in real applications , should be limited by total power dissipation.

Typical Characteristics




Fig.1 Typical Output Characteristics




Fig.2 On-Resistance v.s Gate-Source




Fig.3 Forward Characteristics of Reverse




Fig.4 Gate-Charge Characteristics




Fig.5 Normalized $V_{GS(th)}$ v.s T_J




Fig.6 Normalized $R_{DS(on)}$ v.s T_J

Typical Characteristics




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Unclamped Inductive Switching Waveform

Marking Diagram



Ordering information

Model name	Package	Unit Weight	Base Quantity	Packing Quantity
YFW30P03DF	PDFN3*3-8L	0.0023oz(0.065g)	5000pcs/reel	10000pcs/box 50000pcs/Carton

Package Dimensions

PDFN3*3-8L

Dim	Millimeter		mil	
	Min.	Max.	Min.	Max.
A	0.70	0.85	0.0276	0.0335
A1	-	0.05	-	0.002
b	0.20	0.40	0.008	0.016
c	0.10	0.25	0.004	0.010
D	3.15	3.45	0.124	0.136
D1	3.00	3.25	0.118	0.128
D2	2.29	2.65	0.09	0.104
E	3.15	3.45	0.124	0.136
E1	2.90	3.20	0.114	0.126
E2	1.54	1.94	0.061	0.076
E3	0.28	0.65	0.011	0.026
E4	0.37	0.77	0.015	0.030
E5	0.10	0.30	0.004	0.012
e	0.60	0.70	0.024	0.028
K	0.59	0.89	0.023	0.035
L	0.30	0.50	0.012	0.020
L1	0.06	0.20	0.002	0.008
t	-	0.13	-	0.005
Φ	10°C	14°C	10°C	14°C

Disclaimer

The information presented in this document is for reference only. Guangdong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.