



技术指标(Technical Index):
 1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 (The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
 2. 温度范围(Temperature range): -25° C~+85° C.
 3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
 4. 接触电阻(Contact resistance): ≤0.03Ω.
 5. 绝缘电阻(Insulation resistance): ≥500MΩ.

Number of Contacts	Dimensions mm		
	A	B	C
04	3.00	5.03	11.10
05	4.00	6.03	12.10
06	5.00	7.03	13.10
07	6.00	8.03	14.10
08	7.00	9.03	15.10
09	8.00	10.03	16.10
10	9.00	11.03	17.10
11	10.00	12.03	18.10
12	11.00	13.03	19.10
13	12.00	14.03	20.10
14	13.00	15.03	21.10
15	14.00	16.03	22.10
16	15.00	17.03	23.10
17	16.00	18.03	24.10
18	17.00	19.03	25.10
19	18.00	20.03	26.10
20	19.00	21.03	27.10
21	20.00	22.03	28.10
22	21.00	23.03	29.10
23	22.00	24.03	30.10
24	23.00	25.03	31.10
25	24.00	26.03	32.10
26	25.00	27.03	33.10
27	26.00	28.03	34.10
28	27.00	29.03	35.10
29	28.00	30.03	36.10
30	29.00	31.03	37.10
31	30.00	32.03	38.10
32	31.00	33.03	39.10
33	32.00	34.03	40.10
34	33.00	35.03	41.10
35	34.00	36.03	42.10
36	35.00	37.03	43.10
37	36.00	38.03	44.10
38	37.00	39.03	45.10
39	38.00	40.03	46.10
40	39.00	41.03	47.10

Ordering Information

CT 10 25 2 - NR - ** - *

TYPE: CT-插拔式, LT-立式
 PITCH: 05=0.5mm, 10=1.0mm
 Plastic Height: 20=2.0mm, 25=2.5mm
 No. of Pins: 04~40Pin, 04R=4Pin, 10R=10Pin
 Contact Plating: C0=Tin(镀锡), C2=Gold Flash(全闪), C1=1u" Gold(全金)
 *上接, *下接

序号	品名	材质
1	1.0K型胶芯(H2.5) 1.0K Type Housing(H2.5)	LCP UL94V-0 本色 Natural
2	1.0K型下接端子(H2.5) 1.0K Type Under Terminal(H2.5)	铜合金/表面镀金 Copper Alloy/ Tin Plating
3	1.0K型弹片后盖(H2.5) 1.0K Type Actuator(H2.5)	LCP UL94V-0 黑色 Black
4	1.0K型弹片(H2.5) 1.0K Type Fitting Nail(H2.5)	铜合金/表面镀金 Copper Alloy/ Tin Plating

序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE
1	初版发行	

GENERAL TOLERANCE		制图 DRAWING
DIM	TOL	审核 CHECK
X.X	±0.30	批准 APPROVAL
X.XX	±0.20	比例 SCALE
X.XXX	±0.10	投影 Projection
Angle	±3.0°	

深圳市华灿天禄电子有限公司
 ShenzhenhuaciantianluELECTRONICS CO.,LTD

产品名称 TITLE	1.0 Pitch K型 拉拔卧式 下接 (H=2.5)	版本 REV.	A
产品料号 PART NO.	CT10252-NR-00-D	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1