



QNHCHIP

QND50P02BY

Product Specification

QND50P02BY

20V P-Channel MOSFET




FEATURES

- -20V, -55A
 $R_{DS(ON)}$ Typ = 6.2m Ω @ $V_{GS} = -4.5V$
 $R_{DS(ON)}$ Typ = 8.4m Ω @ $V_{GS} = -2.5V$
- Advanced Trench Technology
- Excellent $R_{DS(ON)}$ and Low Gate Charge

Applications

- Load Switch
- PWM Application
- Power Management

Pin Description



NO.	Symbol	Description
1	G	GATE
2	D	DRAIN
3	S	SOURCE



Absolute Maximum Ratings

(@ $T_C = 25^\circ\text{C}$ unless otherwise specified)

Symbol	Parameter	Value	Units	
V_{DS}	Drain-to-Source Voltage	-20	V	
V_{GS}	Gate-to-Source Voltage	± 12	V	
I_D	Continuous Drain Current	$T_A = 25^\circ\text{C}$	-55	A
		$T_A = 100^\circ\text{C}$	-33	
I_{DM}	Pulsed Drain Current ⁽¹⁾	-220	A	
EAS	Single Pulsed Avalanche Energy ⁽²⁾	39	mJ	
P_D	Power Dissipation	$T_A = 25^\circ\text{C}$	41.6	W
$R_{\theta JC}$	Thermal Resistance, Junction to Case	3	$^\circ\text{C}/\text{W}$	
T_J, T_{STG}	Junction & Storage Temperature Range	-55 to 150	$^\circ\text{C}$	



Electrical Characteristics

(T_J = 25 °C unless otherwise specified)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
Off Characteristics						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	I _D = -250 μA, V _{GS} = 0V	-20	-	-	V
I _{DSS}	Zero Gate Voltage Drain Current	V _{DS} = -20V, V _{GS} = 0V	-	-	-1.0	μA
I _{GSS}	Gate-Body Leakage Current	V _{DS} = 0V, V _{GS} = ±12V	-	-	±100	nA
On Characteristics						
V _{GS(th)}	Gate Threshold Voltage	V _{DS} = V _{GS} , I _D = -250 μA	-0.4	-0.65	-1	V
R _{DS(ON)}	Static Drain-Source ON-Resistance ⁽³⁾	V _{GS} = -4.5V, I _D = -15 A	-	6.2	8.1	mΩ
		V _{GS} = -2.5V, I _D = -10A	-	8.4	11	mΩ
Dynamic Characteristics						
C _{iss}	Input Capacitance	V _{GS} = 0V, V _{DS} = -10V, f = 1MHz	-	2888	-	pF
C _{oss}	Output Capacitance		-	380	-	pF
C _{rss}	Reverse Transfer Capacitance		-	342	-	pF
Q _g	Total Gate Charge	V _{GS} = 0 ~ -4.5V, V _{DS} = -10V, I _D = -15A	-	54	-	nC
Q _{gs}	Gate Source Charge		-	7	-	nC
Q _{gd}	Gate Drain ("Miller") Charge		-	14	-	nC
Switching Characteristics						
t _{d(on)}	Turn-On Delay Time	V _{GS} = -10V, V _{DD} = -10V, I _D = -13A, R _{GEN} = 3	-	13	-	ns
t _r	Turn-On Rise Time		-	105	-	ns
t _{d(off)}	Turn-Off Delay Time		-	145	-	ns
t _f	Turn-Off Fall Time		-	150	-	ns
Drain-Source Diode Characteristics and Max Ratings						
I _S	Maximum Continuous Drain to Source Diode		-	-	-55	A
I _{SM}	Maximum Pulsed Drain to Source Diode Forward		-	-	-220	A
V _{SD}	Drain to Source Diode	V _{GS} = 0V, I _S = -15A	-	-	-1.2	V
t _{rr}	Body Diode Reverse Recovery	I _F = -15A, di/dt = 100A/us	-	26	-	ns
Q _{rr}	Body Diode Reverse Recovery		-	15	-	nC


Notes:

1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
2. EAS condition: T_J = 25 °C, V_{DD} = -10V, V_G = -10V, R_G = 25 Ω, L = 0.5mH, I_{AS} = -12.5A
3. Pulse Test: Pulse Width ≤ 300us, Duty Cycle ≤ 0.5%




Test Circuit


Gate Charge Test Circuit & Waveform




Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching (UIS) Test Circuit & Waveforms




Diode Recovery Test Circuit & Waveforms





Package Mechanical Data(TO-252-3L)



Ref.	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	2.10	2.50	0.083	0.098
A2	0	0.10	0	0.004
B	0.66	0.86	0.026	0.034
B2	5.18	5.48	0.202	0.216
C	0.40	0.60	0.016	0.024
C2	0.44	0.58	0.017	0.023
D	5.90	6.30	0.232	0.248
D1	5.30 REF		0.209 REF	
E	6.40	6.80	0.252	0.268
E1	4.63		0.182	
G	4.47	4.67	0.176	0.184
H	9.50	10.70	0.374	0.421
L	1.09	1.21	0.043	0.048
L2	1.35	1.65	0.053	0.065
V1	7°		7°	
V2	0°	6°	0°	6°

Ordering information

Order Code	Package	V _{DS} (V)	I _D (A)	R _{DS(ON)} (m Ω)	
QND50P02BY	TO-252	-20	-55	V _{GS} =-4.5V	6.2
				V _{GS} =-2.5V	8.4