







NOTE:1


- ELECTRICAL CHARACTERISTICS:
 - CURRENT RATING: 0.5A MAX.
 - IMPEDANCE: 500HM NOMINAL.
- MECHANICAL CHARACTERISTICS:
 - OPERATING TEMP. $-40^{\circ}\sim 90^{\circ}$
 - VEWR UP TO 3GHz: 1.3MAX.
3GHz TO 6GHz: 1.4MAX.
 - DURABILITY: 30CYCLES



RECOMMENDED PCB LAYOUT
GENERAL TOLERANCE ± 0.05

NOTE:2

- HOUSING MATERIAL: LCP, NATURE, UL94V-0.
- TERMINAL MATERIAL: COPPER ALLOY (C2680),
- SHELL MATERIAL: COPPER ALLOY (C5191),



3	GROUND CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
2	INNER CONTACT	1	COPPER ALLOY	Au PLATING OVER NI OVER ALL	
1	HOUSING	1	LCP UL94V-0		
ITEM	DESCRIPTION	Q'TY	MATERIAL	FINISH	REMARK

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		APR.	TITLE: RF BOARD END CONNECTOR, FIRST GENERATION		
.X ± 0.25	X.* $\pm 5^{\circ}$	Alex	DWG NO. RF1-2D		
.XX ± 0.25	.X.* $\pm 3^{\circ}$	Jack	PROJ.  CUSTOMER DRAWING		
.XXX $\pm$	.XX.* $\pm 1^{\circ}$	Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A