



1-Line Ui-directional High Power TVS Diode

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



Features

- * 1500W peak pulse power (8/20 μ s)
- * Low leakage: nA level
- * Low operating voltage: 4.5/5.0V
- * Ultra low clamping voltage
- * One power line protects
- * Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test
 - Air discharge: ± 30 kV
 - Contact discharge: ± 30 kV
 - IEC61000-4-5 (Lightning) 110A (8/20 μ s)
- * RoHS Compliant
- * Package: SOD-323
- * Lead Finish: Sn

Description

The WS4.5D3HV is a ui-directional high power TVS diode, utilizing leading monolithic silicon technology to provide fast response time and low ESD clamping voltage, making this device an ideal solution for protecting voltage sensitive data and power line. The WS4.5D3HV complies with the IEC 61000-4-2 (ESD) standard with ± 15 kV air and ± 8 kV contact discharge. It is assembled into an ultra-small lead-free SOD-323 package. The small size and high ESD surge protection make WS4.5D3HV an ideal choice to protect cell phone, digital cameras, audio players and many other portable applications.

Applications

- * Mobile Phones and Accessories
- * Battery Protection
- * USB VBus
- * Power Line Protection
- * Hand Held Portable Applications

Absolute Maximum Ratings ($T_A=25^\circ\text{C}$ unless otherwise specified)


Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20 μs)	Ppk	1500	W
Peak Pulse Current (8/20 μs)	IPP	110	A
ESD per IEC 61000-4-2 (Air)	VESD	± 30	kV
ESD per IEC 61000-4-2 (Contact)		± 30	
Operating Temperature Range	TJ	-55 to +125	$^\circ\text{C}$
Storage Temperature Range	Tstg	-55 to +150	$^\circ\text{C}$

Electrical Characteristics ($T_A=25^\circ\text{C}$ unless otherwise specified)


Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
Reverse Working Voltage	V_{RWM}				4.5	V
Breakdown Voltage	V_{BR}	$I_T = 1\text{mA}$	5.5			V
Reverse Leakage Current	I_R	$V_{RWM} = 4.5\text{V}$			1.0	μA
Clamping Voltage	V_C	$I_{PP} = 50\text{A}$ (8 x 20 μs pulse)		7.5		V
Clamping Voltage	V_C	$I_{PP} = 110\text{A}$ (8 x 20 μs pulse)		9.5	14	V
Junction Capacitance	C_J	$V_R = 0\text{V}$, $f = 1\text{MHz}$		330	400	pF

Portion Electronics Parameter


Symbol	Parameter
I_T	Test Current
I_{PP}	Maximum Reverse Peak Pulse Current
V_C	Clamping Voltage @ I_C




Typical Performance Characteristics ($T_A=25^{\circ}\text{C}$ unless otherwise Specified)




Junction Capacitance vs. Reverse Voltage




Clamping Voltage vs. Peak Pulse Current




Peak Pulse Power vs. Pulse Time



IEC61000-4-2 Pulse Waveform




Power Derating Curve




8 X 20us Pulse Waveform

Plastic surface mounted package

SOD-323



SOLDERING FOOTPRINT



Unit : mm