



SPECIFICATIONS

- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 100V AC, DC
- 3、Temperatuer Range: -25℃~ +85℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000mΩ Min
- 6、Withstanding Voltang: 800V AC/minute
- 7、Material: Wafer LCP UL94V-0(2)
PIN Brass Tin-plated

Circuit	Part NO.	Dimensions mm		
		A	B	C
2	HC-PH-2A-LCP-05	2.00	6.00	4.90
3	HC-PH-3A-LCP-05	4.00	8.00	6.90
4	HC-PH-4A-LCP-05	6.00	10.00	8.90
5	HC-PH-5A-LCP-05	8.00	12.00	10.90
6	HC-PH-6A-LCP-05	10.00	14.00	12.90
7	HC-PH-7A-LCP-05	12.00	16.00	14.90
8	HC-PH-8A-LCP-05	14.00	18.00	16.90
9	HC-PH-9A-LCP-05	16.00	20.00	18.90
10	HC-PH-10A-LCP-05	18.00	22.00	20.90
11	HC-PH-11A-LCP-05	20.00	24.00	22.90
12	HC-PH-12A-LCP-05	22.00	26.00	24.90
13	HC-PH-13A-LCP-05	24.00	28.00	26.90
14	HC-PH-14A-LCP-05	26.00	30.00	28.90
15	HC-PH-15A-LCP-05	28.00	32.00	30.90
16	HC-PH-16A-LCP-05	30.00	34.00	32.90
17	HC-PH-17A-LCP-05	32.00	36.00	34.90
18	HC-PH-18A-LCP-05	34.00	38.00	36.90
19	HC-PH-19A-LCP-05	36.00	40.00	38.90
20	HC-PH-20A-LCP-05	38.00	42.00	40.90

Ordering Information

HC-PH - N*** - LCP - * - 05

Pin Type Colour
 V=孔深
 A=间距
 AM=定位间距
 默认=本色
 B=蓝色
 L=绿色
 R=黄色
 P=紫色
 V=银色
 Ø=镀金
 Ø=镀锡

			GENREL TOLERANCE	制图	深圳市华灿天禄电子有限公司			
			DIM TOL	DRAWING	ShenzhenhuacantianluELECTRONICS CO., LTD			
			X.X ±0.30	审核	产品名称	PH (2.00)单排 直针	版本	A
			X.XX ±0.20	CHECK	产品料号	HC-PH-NA-LCP-05	REV.	
			X.XXX ±0.10	批准	PART NO.		UNIT	mm
1	初版发行	日期	Angle ±3.0°	APPROVAL	材料		SHEET	1/1
序号	变更内容	MODIFY DATE		SCALE	MATERIAL			
				投影				