

3W Surface Mount Zener Diodes

FEATURES

- ◆ Glass passivated chip
- ◆ Built-in strain relief
- ◆ Low inductance
- ◆ High peak reverse power dissipation
- ◆ Low reverse leakage
- ◆ For use in stabilizing and clipping with high power rating
- ◆ RoHS compliant

MECHANICAL DATA

- ◆ Case: SMA Molded plastic
- ◆ Lead: Solderable per MIL-STD-750, method 2026
- ◆ Epoxy: UL 94V-0 rate flame retardant
- ◆ Polarity: Color band denotes cathode end except Bipolar
- ◆ Mounting position: Any

Pinning


1.Cathode	2.Anode
	
DO-214AC/SMA	

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Symbol	Value	Unit
Power Dissipation at T _C =75°C	P _D	3.0	W
Forward Voltage at I _F = 200 mA	V _F	1.5	V
Junction Temperature Range	T _J	55 ~ +175	°C
Storage Temperature Range	T _S	-55 ~ +175	°C

Fig.1 Forward Current Derating Curve



Characteristics at Ta = 25°C

(TL = 30°C unless otherwise noted, VF = 1.5 V Max. @ IF = 200 mA(DC) for all types)

Type	Marking	Nominal Zener Voltage ⁽³⁾				Zener Impedance ⁽⁴⁾			Leakage Current		Maximum DC Zener Current
		V _z			I _{zT}	Z _{zT} @ I _{zT}	Z _{zK} @ I _{zK}	I _r @ V _R			
		Min (V)	Nom (V) ⁽²⁾	Max (V)	(mA)	(Ω)	(Ω)	(mA)	(μA)	(V)	I _{zM} (mA)(DC)
3SMA5913B	H13B	3.13	3.3	3.47	227.3	10	500	1	100	1	817
3SMA5914B	H14B	3.42	3.6	3.78	208.3	9	500	1	100	1	749
3SMA5915B	H15B	3.70	3.9	4.10	192.0	4.5	500	1	100	1	691
3SMA5916B	H16B	4.08	4.3	4.52	174.0	4.5	500	1	50	1	627
3SMA5917B	H17B	4.46	4.7	4.94	160.0	4	500	1	50	1	573
3SMA5918B	H18B	4.84	5.1	5.36	147.0	3.5	550	1	10	1	528
3SMA5919B	H19B	5.32	5.6	5.88	134.0	2.5	600	1	10	2	481
3SMA5920B	H20B	5.89	6.2	6.51	121.0	1.5	700	1	10	3	435
3SMA5921B	H21B	6.46	6.8	7.14	110.0	2	700	1	10	4	393
3SMA5922B	H22B	7.12	7.5	7.88	100	2	700	0.5	10	5	360
3SMA5923B	H23B	7.79	8.2	8.61	91.0	2.3	700	0.5	10	6	330
3SMA5924B	H24B	8.64	9.1	9.56	82.0	2.5	700	0.5	10	7	297
3SMA5925B	H25B	9.5	10	10.5	75.0	3.5	700	0.25	10	7.6	270
3SMA5926B	H26B	10.45	11	11.55	68.0	4.0	700	0.25	1	8.4	246
3SMA5927B	H27B	11.4	12	12.6	63.0	4.5	700	0.25	1	9.1	225
3SMA5928B	H28B	12.35	13	13.65	58.0	4.5	700	0.25	1	9.9	208
3SMA5929B	H29B	14.25	15	15.75	50.0	5.5	700	0.25	1	11.4	180
3SMA5930B	H30B	15.2	16	16.8	47.0	5.5	700	0.25	1	12.2	169
3SMA5931B	H31B	17.1	18	18.9	42.0	6	750	0.25	1	13.7	150
3SMA5932B	H32B	19	20	21	37.0	7	750	0.25	1	15.2	135
3SMA5933B	H33B	20.9	22	23.1	34.0	8	750	0.25	1	16.7	123
3SMA5934B	H34B	22.8	24	25.2	31.0	9	750	0.25	1	18.2	112
3SMA5935B	H35B	25.65	27	28.35	28.0	10	750	0.25	1	20.6	100
3SMA5936B	H36B	28.5	30	31.5	25.0	16	1000	0.25	1	22.5	90
3SMA5937B	H37B	31.35	33	34.65	23.0	20	1000	0.25	1	25.1	82
3SMA5938B	H38B	34.2	36	37.8	21.0	22	1000	0.25	1	27.4	75
3SMA5939B	H39B	37.05	39	40.95	19.0	28	1000	0.25	1	29.7	69
3SMA5940B	H40B	40.85	43	45.15	17.0	33	1500	0.25	1	32.7	63
3SMA5941B	H41B	44.65	47	49.35	16.0	38	1500	0.25	1	35.6	57
3SMA5942B	H42B	48.45	51	53.55	15.0	45	1500	0.25	1	38.8	53
3SMA5943B	H43B	53.2	56	58.8	13.0	50	2000	0.25	1	42.6	48
3SMA5944B	H44B	58.9	62	65.1	12.0	55	2000	0.25	1	47.1	44
3SMA5945B	H45B	64.6	68	71.4	11.0	70	2000	0.25	1	51.7	40
3SMA5946B	H46B	71.25	75	78.75	10.0	85	2000	0.25	1	56	36
3SMA5947B	H47B	77.9	82	86.1	9.1	95	3000	0.25	1	62.2	33
3SMA5948B	H48B	86.45	91	95.55	8.2	115	3000	0.25	1	69.2	30
3SMA5949B	H49B	95	100	105	7.5	160	3000	0.25	1	76	27
3SMA5950B	H50B	104.5	110	115.5	6.8	225	4000	0.25	1	83.6	25
3SMA5951B	H51B	114	120	126	6.3	300	4500	0.25	1	91.2	22
3SMA5952B	H52B	123.5	130	136.5	5.8	375	5000	0.25	1	98.8	21
3SMA5953B	H53B	142.5	150	157.5	5.0	550	6000	0.25	1	114	18
3SMA5954B	H54B	152	160	168	4.7	625	6500	0.25	1	121.6	17
3SMA5955B	H55B	171	180	189	4.2	700	7000	0.25	1	136.8	15
3SMA5956B	H56B	190	200	210	3.7	875	8000	0.25	1	152	13

Marking Diagram



Ordering information


Package	Packing Description	Packing Quantity
DO-214AC SMA	Tape/Reel, 13"reel	5000PCS/Reel 50000PCS/Cartron

Package Dimensions

DO-214AC SMA

Dim.	Millimeter(mm)		mil	
	Min.	Max.	Min.	Max.
A	1.9	2.45	75	96
D	4.0	4.5	157	181
E	2.5	2.8	100	110
H _E	4.7	5.2	185	205
c	0.15	0.31	6	12
e	1.3	1.8	51	71
g	0.9	1.5	35	59
b	0.05	0.2	2	7.9
a	0.3		12	

The recommended mounting pad size



Unit : $\frac{\text{mm}}{(\text{mil})}$

Disclaimer

The information presented in this document is for reference only. GuangDong Youfeng Microelectronics Co.,Ltd. reserves the right to make changes without notice for the specification of the products displayed herein to improve reliability, function or design or otherwise. The product listed herein is designed to be used with ordinary electronic equipment or devices, and not designed to be used with equipment or devices which require high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), YFW or anyone on its behalf, assumes no responsibility or liability for any damages resulting from such improper use of sale. This publication supersedes & replaces all information previously supplied. For additional information, please visit our website <https://www.yfwdiode.com>, or consult YFW sales office for further assistance.