

SOT-23 Plastic-Encapsulate Transistors

Features


- Built-in bias resistors enable the configuration of an inverter circuit without connecting external input resistors(see equivalent circuit)
- The bias resistors consist of thin-film resistors with complete isolation to allow positive biasing of the input.They also have the advantage of almost completely eliminating parasitic effects
- Only the on/off conditions need to be set for operation, making device design easy

Supply Voltage
VCC 50V
Collector Current
0.05 Ampere


Mechanical Data

- Case: SOT-23
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026

SOT-23



Function Diagram



Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SOT-23	R1	0.0085	3000	15000	150000	7"

Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	VALUE
Supply Voltage	V _{CC}	V	50
Input Voltage	V _{IN}	V	-10~+40
Output Current	I _O	mA	50
Power Dissipation	P _D	mW	200
Storage temperature	T _{stg}	°C	-55 ~+150
Junction temperature	T _j	°C	-55 ~+150





Small-signal Characteristics

ITEM	SYMBOL	Condition	UNIT	Min	Typ	Max
Transition frequency	f _T	I _o = 5mA, V _o = 10V	MHz	-	250	-

● **Electrical Characteristics** (Ta=25°C Unless otherwise noted)

PARAMETER	SYMBOL	UNIT	Condition	Min	Typ	Max
Input voltage	$V_{I(off)}$	V	$I_o=100\mu A, V_{cc}=5V$	0.5	-	-
	$V_{I(on)}$		$I_o=10mA, V_o=0.3V$	-	-	3
Output voltage	$V_{O(on)}$		$I_o/I_i=10mA/0.5mA$	-	-	0.3
Input current	I_i	mA	$V_i=5V$	-	-	0.88
Output current	$I_{O(off)}$	μA	$V_{cc}=50V, V_i=0V$	-	-	0.5
DC Current Gain	G_i	-	$V_o=5V, I_o=5mA$	30	-	-
Input resistance	R_i	k Ω	-	7	10	13
Resistance ratio	R_2/R_1	-	-	0.8	1	1.2

● **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)



● Package Outline Dimensions (SOT-23)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	0.90	1.15	0.035	0.045
A1	-	0.10	-	0.004
A2	0.90	1.05	0.035	0.041
b	0.30	0.50	0.012	0.020
c	0.10	0.20	0.004	0.008
D	2.80	3.00	0.110	0.118
E	1.20	1.40	0.047	0.055
E1	2.25	2.55	0.089	0.100
e	0.950TYP		0.037TYP	
e1	1.80	2.00	0.071	0.079
L	0.550REF		0.022REF	
L1	0.30	0.50	0.012	0.020
θ	-	8°	-	8°

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
J	0.80	-	0.031	-
K	-	0.90	-	0.035
M	2.00	-	0.078	-
N	-	1.90	-	0.074