



Product packaging logic diagram



Pin Configuration

Features

- Low trigger current IFT 10mA
- Peak off state voltage 600V
- Load current 0.3, 0.6, 0.9, 1.2A
- High isolation voltage between input and output (Viso = 5000Vrms)
- Operating Temperature: -55°C~100°C
- Environmentally friendly products, compliant with CQC, UL, and VDE requirements

Mechanical Data

- Case: DIP7、DIP7-M、SMD7
- Molding Compound: UL Flammability Classification Rating 94V-0
- Terminals: Matte tin-plated leads; solder ability-per MIL-STD-202, Method 208

Applications

- Commonly used in motor speed control systems, Power regulation system and follow-up system, Control of high-power equipment through low-power controls.
- Mainly used for motor speed control and temperature control.
- In the power system for power switches, Charging pile control and battery management system (BMS) ,Achieve precise control of voltage/current and equipment protection.
- Vehicle power management, Drive motor control and charge/discharge management, Improving vehicle energy efficiency and safety.
- In fiber optic communication equipment, routers and medical devices, signal isolation and power control in the middle, Ensure stable operation of equipment.



Ordering Information


XL RX223 (M) (G) - (U) (N) (Y)
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Brand(XL)
- ② Product series(X:0,1,2,3)
- ③ Package type (DIP7: DIP7-M: M, SMD7: S)
- ④ Halogen option (None :Halogen free)
- ⑤ Lead frame (None: Copper)
- ⑥ Customer option 1 (0-9 or A-Z or none)
- ⑦ Customer option 2 (0-9 or A-Z or none)

Part Number	Package	Shipping Quantity	Marking Code
XLRX223	DIP7	45pcs / Tube	XLRX223
XLRX223M	DIP7-M	45pcs / Tube	XLRX223
XLRX223S	SMD7	1000pcs / Tape & Reel	XLRX223

Marking Information

- " XL" denotes brand
- " X" denotes IFT digit: 0, 1, 2, 3
- " Y" denotes Year : A(2024), B(2025), C(2026)
- " WW" denotes Week' s number
- " N" denotes the day of Week



Maximum Ratings (@ T_A = 25°C unless otherwise specified)

Parameter		Symbol	Value	Unit	
Input	Forward Current	IF	50	mA	
	Reverse Voltage	VR	5	V	
	Peak Forward Current*1	IFP	1	A	
	Power Dissipation	PD	75	mW	
Output	Power Dissipation	PC	300	mW	
	Off-state Output Terminal Voltage	VDRM	600	V	
	ON-state RMS current	XLR0223	IT(RMS)	0.3	A
		XLR1223		0.6	
		XLR2223		0.9	
		XLR3223		1.2	
	Non-repetitive surge current*3	XLR0223	ITSM	3	A
		XLR1223		6	
XLR2223		9			
XLR3223		12			

Thermal Characteristics

Parameter	Symbol	Value	Unit
Total Power Dissipation	P _{TOT}	375	mW
Isolation Voltage *1	V _{ISO}	5000	V _{rms}
Operating Temperature	T _{OPR}	-40 ~ +85	°C
Storage Temperature Range	T _{STG}	-40 ~ +125	°C
Soldering Temperature *2	T _{SOL}	260	°C

Notes:

- 40 to 60% RH, AC for 1 minute. At this time, pins 1, 2 & 3 are shorted, and pins 4, 5 & 6 are shorted together.
- For 10 seconds







Electrical Characteristics (@ T_A = 25°C unless otherwise specified)


Parameter		Symbol	Test Condition	Min.	Typ.	Max.	Unit
Input	Forward Voltage	VF	IF=20mA	-	1.2	1.4	V
	Reverse Leakage current	IR	VR=5V	-	-	10	μA
	Input Capacitance	CIN	f=1kHz	-	45	-	PF
Output	Peak Blocking Current	IDRM	VDRM =600 V IF=0mA	-	-	100	μA
	Peak on-state voltage	VTM	IF = 10mA, ITM = MAX	-	-	2.5	V
	Critical Rate of Rise off-state voltage	dv /dt	VPEAK = Rated VDRM	200	-	-	V/ μs
Transfer Characteristics	Minimum trigger Current	IFT	VD=6V, RL=100Ω	-	-	10	mA
	Holding Current	IH	Terminal Voltage from "ON" to "OFF" "ON" state IF=0mA	-	-	25	mA
	Turn On Time	Ton	IF= 20mA, VD= 6V, RL=100Ω	-	10	100	us
	Isolation Resistance	RIO	VIO=500VDC	1X10 ¹¹	-	-	Ω
	Isolation Capacitance	CIO	f=1MHz	-	0.25	-	PF

Notes:

1. The additional test voltage should be within dv/dt rated value.
2. This is static dv/dt, dv/dt is converted with changes of loading for the driven thyristor.
3. It is guaranteed that all devices trigger when IF value is less than or equal to the maximum value of IFT.


Ratings and Characteristics Curves (@ $T_A = 25^\circ\text{C}$ unless otherwise specified)






Package Outline Dimensions (unit: mm)


DIP7




DIP7-M




SMD7



SOLDERING FOOTPRINT (unit: mm)



Reflow soldering




	Symbol	Min	Max	Unit
Preheat temperature	T_s	150	200	°C
Preheat time	t_s	60	120	s
Ramp-up rate(T_L to T_P)	-	-	3	°C/s
Liquidus temperature	T_L	217		°C
Time above T_L	t_L	60	150	s
Peak temperature	T_P	-	260	°C
Time during which T_c is between ($T_P - 5$) and T_P	t_p	-	30	s
Ramp-down rate(T_P to T_L)	-	-	6	°C/s

Note:

Reflow soldering is recommended at the temperatures and times shown, no more than three times.

Wave soldering



Profile feature	
Average ramp-up rate	~200°C/s
Heating rate during preheat	1°C/s to 2°C/s typical; 4°C/s maximum
Final preheat temperature T_s	~130°C
Preheat time (25°C to T_s)	> 60s
Peak temperature T_p	260°C
Time within peak temperature t_p	10s
Ramp-down rate	5°C/s maximum

Soldering with hand soldering iron

- Hand soldering iron is only used for product rework or sample testing.
- Hand soldering iron requirements: Temperature: 360 °C + 5°C within 3s.

Packing

Package Type	Packing Form	Quantity per Tube & Reel	Quantity per Box	Quantity per Carton	Antistatic Bag Specification	Box Specification	Carton Specification	Note
DIP7	Tube(500mm)	45pcs/tube	25 tubes /box	12 boxes /ctn	190*670mm	520*105*50mm	545*372*235mm	Straight insert type material tube
DIP7-M	Tube(500mm)	45pcs/tube	25 tubes /box	12 boxes /ctn	190*670mm	520*105*50mm	545*372*235mm	Seagull foot (M foot) tube
SMD7	Reel(φ330mm)	1000pcs/reel	2 reels /box	5 boxes /ctn	380*420mm	350*340*60mm	365*330*370mm	Guard band 200mm /min.

■ Summary table

■ DIP8/DIP8-M (Tube)

Qty/tube: 45pcs. Qty/box: 1125pcs.

Qty/ctn : 13500pcs.


Schematic: (unit:mm)

■ SMD8 (Reel)

Qty/reel: 1000pcs. Qty/box: 2000pcs.

Qty/ctn : 10000pcs.

Schematic: (unit:mm)



IMPORTANT NOTICE

XINGLIGHT reserves the right to make changes without further notice to any product herein to make corrections, modifications, improvements, or other changes. XINGLIGHT does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others.