


VOLTAGE RANGE
40 Volts
CURRENT
3.0 Ampere

FEATURES

- * Ideal for surface mount applications
- * Easy pick and place
- * Built-in strain relief
- * Low forward voltage drop

MECHANICAL DATA

- * Case: Molded plastic
- * Epoxy: UL 94V-0 rate flame retardant
- * Terminals: Solder plated, solderable per MIL-STD-202F method 208 guranteed
- * Polarity: Color band denotes cathode end
- * Mounting position: Any



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unieess otherwies specified.
Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

TYPE NUMBER	K34	UNITS
Maximum Recurrent Peak Reverse Voltage	40	V
Maximum RMS Voltage	28	V
Maximum DC Blocking Voltage	40	V
Maximum Average Forward Rectified Current	3.0	A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)	80	A
Maximum Instantaneous Forward Voltage at 3.0A	0.55	V
Maximum DC Reverse Current Ta=25°C	0.1	mA
at Rated DC Blocking Voltage Ta=100°C	5	mA
Typical Junction Capacitance (Note1)	300	pF
Typical Thermal Resistance R _{JL} (Note 2)	10	°C/W
Operating Temperature Range T _J	-65 — +150	°C
Storage Temperature Range T _{STG}	-65 — +150	°C

NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
2. Thermal Resistance Junction to Lead.

RATING AND CHARACTERISTIC CURVES

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL FORWARD CHARACTERISTICS




FIG.3 - TYPICAL REVERSE CHARACTERISTICS




FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT





FIG.5-TYPICAL JUNCTION CAPACITANCE





Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C



Package Dimensions & Suggested Pad Layout

SOD123FL



SOD123FL		
Dim	Min	Max
A	1.00	1.20
b	0.80	1.10
c	0.12	0.20
D	1.75	1.95
E	2.60	2.90
He	3.55	3.80
L2	0.50	0.85
All Dimensions in mm		

Dimensions	Value (in mm)
C	3.25
G	2.00
X	1.25
X1	4.50
Y	1.50

Tape & reel specification

Tape		Symbol	Dimension (mm)		
<p>The diagram shows a top view of a carrier tape with dimensions P0, P1, P2, D0, E, F, W, D1, and D0. It also includes two cross-sectional views: SECTION: A-A showing the width A0, and SECTION: B-B showing the height T, width B0, and offset K0.</p>		P0	4.00±0.20		
		P1	4.00±0.20		
		P2	2.00±0.20		
		D0	1.55±0.15		
		D1	1.00±0.20		
		E	1.75±0.20		
		F	3.50±0.25		
		W	8.00±0.20		
		A0	1.85±0.20		
		B0	3.95±0.20		
		K0	1.30±0.20		
		T	0.21±0.10		
		7" Reel		D2	178.0±5.0
		<p>The diagram shows a top view of a 7-inch reel with diameter D2 and a side view showing dimensions D4, D3, and W1.</p>		D3	55.0Min.
D4	10.0±2.5				
W1	11.5±2.5				
Quantity: 3000PCS					