


**SOT-23 Switching Diode 开关二极管**

**Internal Configuration & Device Marking 内部结构与产品打标**

Type 型号	MMBD4148A	MMBD4148CA	MMBD4148CC	MMBD4148SE
Pin 管脚				
Mark 打标	5H	D6	D5	D4

**Absolute Maximum Ratings 最大额定值**





Characteristic 特性参数	Symbol 符号	Rat 额定值	Unit 单位
Peak Reverse Voltage 反向峰值电压	$V_{RRM}$	100	V
Reverse Work Voltage 反向工作电压	$V_{RWM}$		
DC Reverse Voltage 直流反向电压	$V_R$		
Forward Work Current 正向工作电流	$I_F(I_O)$	200	mA
Peak Forward Current 正向峰值电流	$I_{FM}$	300	mA
Power dissipation 耗散功率	$P_D(T_a=25^\circ\text{C})$	225	mW
Thermal Resistance J-A 结到环境热阻	$R_{\theta JA}$	555	$^\circ\text{C}/\text{W}$
Junction and Storage Temperature 结温和储藏温度	$T_J, T_{stg}$	-55to+150 $^\circ\text{C}$	

**Electrical Characteristics 电特性**


( $T_A=25^\circ\text{C}$  unless otherwise noted 如无特殊说明, 温度为  $25^\circ\text{C}$ )

Characteristic 特性参数	Symbol 符号	Min 最小值	Max 最大值	Unit 单位
Reverse Breakdown Voltage 反向击穿电压 ( $I_R=100\mu\text{A}$ )	$V_{(BR)}$	100	—	V
Reverse Leakage Current( $V_R=25\text{V}$ ) 反向漏电流( $V_R=75\text{V}$ )	$I_R$	—	25 5	nA $\mu\text{A}$
Forward Voltage( $I_F=50\text{mA}$ ) 正向电压( $I_F=150\text{mA}$ )	$V_F$	—	1 1.25	V
Diode Capacitance 二极管电容( $V_R=0\text{V}$ , $f=1\text{MHz}$ )	$C_D$	—	4	pF
Reverse Recovery Time 反向恢复时间	$T_{rr}$	—	4	nS

■ Typical Characteristic Curve 典型特性曲线



■ Dimension 外形封装尺寸



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.050	0.055
E1	2.250	2.550	0.089	0.100
e	0.900	1.00	0.035	0.039
e1	1.800	2.000	0.071	0.079
L	0.500	0.600	0.020	0.024
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°