


© 2021 TE Connectivity. All Rights Reserved.


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
1		NEW DRAWING	08ARP21	K.Z	J.Z
A		RELEASED	24MAR22	K.Z	J.Z
A1		UPDATE NOTE	12AUG22	K.Z	J.Z

2382718-1




PLUG SHOWN WITH SECONDARY LOCK IN CLOSE POSITION (NOT THE DELIVERY CONDITION)




1


2382718-2




2382718-3









2382718-4




2382718-5



2382718-6



2382718-1 AS SHOWN



NOTES:

- 1. DELIVERY CONDITION: TPA IN PRE-LOCK POSITION, IF TPA UNEXPECTED BECOME ENGAGED, PLEASE MOVE TPA TO PRE-LOCK POSITION.
- 2. MATING PART TE P/N: X-2389701-X SUITABLE INTERFACE: 114-160096.
- 3. CONNECTOR VALIDATED TO LV214.
- 4. APPLICABLE TERMINAL PART NUMBERS: X-1703930-X

PART NO	REV	CODING	COLOR	MATERIAL	WEIGHT(g)
2382718-6	A	F	VIOLET	PA66	3.98
2382718-5	A	E	BROWN	PA66	3.98
2382718-4	A	D	GREEN	PA66	3.98
2382718-3	A	C	BLUE	PA66	3.98
2382718-2	A	B	GREY	PA66	3.98
2382718-1	A	A	BLACK	PA66	3.98

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN: K.ZHOU 08APR2021
 CHK: T.DONG 08APR2021
 APVD: J.ZONG 08APR2021

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 ±0.3
 0 PLC ±
 1 PLC ±0.1
 2 PLC ±0.01
 3 PLC ±0.001
 4 PLC ±0.0001
 ANGLES ±
 FINISH -

MATERIAL: SEE TABLE

PRODUCT SPEC: 108-160392
 APPLICATION SPEC: -
 WEIGHT: SEE TABLE

CUSTOMER DRAWING

TE TE Connectivity

NAME: 40POS NANOMQS , REC HSG

SIZE: A3 CAGE CODE: 00779 DRAWING NO: C-2382718 RESTRICTED TO: -


SCALE: 1:1 SHEET: 1 OF 2 REV: A1

Printed on 12 Aug 2022 11:03 (China Standard Time) from TE460523













© 2021 TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			




PLUG SHOWN WITH SECONDARY LOCK IN CLOSE POSITION (NOT THE DELIVERY CONDITION)



NOTES:

1. DELIVERY CONDITION: TPA IN PRE-LOCK POSITION, IF TPA UNEXPECTED BECOME ENGAGED, PLEASE MOVE TPA TO PRE-LOCK POSITION.
2. MATING PART TE P/N: X-2389701-X
SUITABLE INTERFACE: 114-160096.
3. CONNECTOR VALIDATED TO LV214
4. APPLICABLE TERMINAL PART NUMBERS: X-2291853-X

PART NO	REV	CODING	COLOR	MATERIAL	WEIGHT(g)
1-2382718-6	A	F	VIOLET	PA66	3.75
1-2382718-5	A	E	BROWN	PA66	3.75
1-2382718-4	A	D	GREEN	PA66	3.75
1-2382718-3	A	C	BLUE	PA66	3.75
1-2382718-2	A	B	GREY	PA66	3.75
1-2382718-1	A	A	BLACK	PA66	3.75



ITEM	22PIN	9PIN
DIM.A	44.2	18.2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.ZHOU 08APR2021
DIMENSIONS: mm		CHK T.DONG 08APR2021
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J.ZONG 08APR2021
0 PLC ±0.3		PRODUCT SPEC 108-160392
1 PLC ±0.1		APPLICATION SPEC -
2 PLC ±0.01		WEIGHT SEE TABLE
3 PLC ±0.001		CUSTOMER DRAWING
4 PLC ±0.0001		
ANGLES ±		
FINISH -		
MATERIAL SEE TABLE		
-		

TE TE Connectivity

NAME
40POS NANOMQS , REC HSG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2382718

RESTRICTED TO
-

SCALE
1:1

SHEET
2 OF 2

REV
A1

Printed on 12 Aug 2022 11:03 (China Standard Time) from TE460523