

SMB Surface Mount Schottky Barrier Rectifier

Features

- High efficiency operation
- Metal silicon junction,majority carrier conduction
- Ultra low forward voltage drop,low power losses
- High forward surge current capability

Reverse Voltage
40 V
Forward Current
3 Ampere


Applications

For use in low voltage,high frequency inverters,free wheeling,and polarity protection applications.



Mechanical Data

- Case: DO-214AA(SMB)
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Cathode line denotes the cathode end

DO-214AA(SMB)



Function Diagram



Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	SK34B
Device marking code			SK34B
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	V	40
Maximum RMS Voltage	V_{RMS}	V	28
Maximum DC blocking Voltage	V_{DC}	V	40
Maximum Average Forward Rectified Current @60Hz sinewave, Resistance load,TL (Fig.1)	$I_{F(AV)}$	A	3.0
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I_{FSM}	A	100
Storage temperature	T_{stg}	°C	-65 ~ +150
Junction temperature	T_j	°C	-65 ~ +150
Typical Thermal Resistance	$R_{\theta J-L}$	°C /W	10





Electrical Characteristics

(Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	SK34B
Maximum instantaneous forward voltage	$I_F=3.0A$	V_F	V	0.55
Maximum DC reverse current at rated DC blocking voltage	$V_R=V_{DC}, T_A=25^{\circ}C$	I_{R1}	mA	0.1
	$V_R=V_{DC}, T_A=100^{\circ}C$	I_{R2}		5
Typical junction capacitance	4.0V DC, 1MHz	C_J	pF	300

Ratings And Characteristics Curves

(Ta=25°C Unless otherwise specified)



● Ordering Information

PACKAGE	PACKAGE CODE	UNIT WEIGHT(g)	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
SMB	R3	0.098	3000	6000	48000	13"

● Package Outline Dimensions (SMB/DO-214AA)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.85	2.21	0.073	0.087
B	4.25	4.85	0.167	0.191
C	3.30	3.94	0.130	0.155
D	2.15	2.65	0.085	0.104
E	0.75	1.52	0.030	0.060
F	-	0.203	-	0.008
G	5.08	5.59	0.200	0.220
H	0.15	0.31	0.006	0.012

Cathode Band

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
M	2.26	-	0.089	-
J	2.10	-	0.085	-
K	-	2.74	-	0.107