



General Description

The HSS2N10A is the high cell density trench N-ch MOSFETs, which provide excellent RDS(on) and gate charge for most of the synchronous buck converter applications.

The HSS2N10A meet the RoHS and Green Product requirement with full function reliability approved.


Product Summary

V_{DS}	100	V
$R_{DS(ON),typ}$	220	mΩ
I_D	2	A

Features

- Green Device Available
- Super Low Gate Charge
- Excellent Cdv/dt effect decline
- Advanced high cell density Trench Technology

SOT-23S Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	100	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_A=25^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10V^1$	2	A
$I_D@T_A=70^\circ\text{C}$	Continuous Drain Current, $V_{GS} @ 10V^1$	1.6	A
I_{DM}	Pulsed Drain Current ²	8	A
$P_D@T_A=25^\circ\text{C}$	Total Power Dissipation ³	0.72	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient(steady state) ¹	---	174	$^\circ\text{C/W}$
	Thermal Resistance Junction-ambient($t < 10s$) ¹	---	146	$^\circ\text{C/W}$



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V$, $I_D=3A$	---	220	260	$m\Omega$
		$V_{GS}=4.5V$, $I_D=2A$	---	240	280	$m\Omega$
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1.0	1.4	2.0	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=100V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	1	μA
		$V_{DS}=100V$, $V_{GS}=0V$, $T_J=55^\circ\text{C}$	---	---	10	
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
R_g	Gate Resistance	$V_{DS}=0V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	2	---	Ω
Q_g	Total Gate Charge (10V)	$V_{DS}=50V$, $V_{GS}=10V$, $I_D=2A$	---	7.3	---	nC
Q_{gs}	Gate-Source Charge		---	1.2	---	
Q_{gd}	Gate-Drain Charge		---	1.7	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=50V$, $V_{GS}=10V$, $R_G=2\Omega$ $I_D=2A$	---	6	---	ns
T_r	Rise Time		---	11	---	
$T_{d(off)}$	Turn-Off Delay Time		---	10	---	
T_f	Fall Time		---	6	---	
C_{iss}	Input Capacitance	$V_{DS}=50V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	288	---	pF
C_{oss}	Output Capacitance		---	11	---	
C_{rss}	Reverse Transfer Capacitance		---	9	---	

Diode Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,4}	$V_G=V_D=0V$, Force Current	---	---	2	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=1A$, $T_J=25^\circ\text{C}$	---	---	1.2	V

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3.The power dissipation is limited by 150°C junction temperature
- 4.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.



Typical Characteristics




Fig.1 Output Characteristic




Fig.2 On-Resistance vs. Drain Current




Fig.3 Transfer Characteristic




Fig.4 On-Resistance vs. Junction Temperature




Fig.5 Safe Operation Area




Fig.6 Capacitance Characteristic




Fig.7 Gate-Charge Characteristic




Fig.8 Body Diode Characteristic




Fig.9 Switching Time Waveform





Fig.10 Gate Charge Waveform



Ordering Information

Part Number	Package code	Packaging
HSS2N10A	SOT-23S	3000/Tape&Reel

SOT-23S Package Outline



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°



HSS2N10A TOP Marking

