

General Description

The HSK0008 is the high cell density trench N-ch MOSFETs, which provides excellent $R_{DS(on)}$ and efficiency for most of the small power switching and load switch applications.

The HSK0008 meet the RoHS and Green Product requirement with full function reliability approved.


Product Summary

V_{DS}	100	V
$R_{DS(ON),max}$	310	m Ω
I_D	2.2	A

Features

- Green Device Available
- Super Low Gate Charge
- Excellent C_{dv}/dt effect decline
- Advanced high cell density Trench Technology

SOT-89 Pin Configuration



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	100	V
V_{GS}	Gate-Source Voltage	± 20	V
$I_D@T_A=25^{\circ}C$	Continuous Drain Current, V_{GS} @ 10V ¹	2.2	A
$I_D@T_A=70^{\circ}C$	Continuous Drain Current, V_{GS} @ 10V ¹	1.7	A
I_{DM}	Pulsed Drain Current ²	5.8	A
$P_D@T_A=25^{\circ}C$	Total Power Dissipation ³	1.5	W
T_{STG}	Storage Temperature Range	-55 to 150	$^{\circ}C$
T_J	Operating Junction Temperature Range	-55 to 150	$^{\circ}C$

Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction-ambient ¹	---	85	$^{\circ}C/W$
$R_{\theta JC}$	Thermal Resistance Junction-Case ¹	---	36	$^{\circ}C/W$



Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V$, $I_D=250\mu A$	100	---	---	V
$R_{DS(ON)}$	Static Drain-Source On-Resistance ²	$V_{GS}=10V$, $I_D=2A$	---	260	310	m Ω
		$V_{GS}=4.5V$, $I_D=1A$	---	270	320	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS}=V_{DS}$, $I_D=250\mu A$	1.0	1.5	2.5	V
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=80V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	1	μA
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=80V$, $V_{GS}=0V$, $T_J=25^\circ\text{C}$	---	---	5	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 20V$, $V_{DS}=0V$	---	---	± 100	nA
gfs	Forward Transconductance	$V_{DS}=5V$, $I_D=2A$	---	5.4	---	S
Q_g	Total Gate Charge (10V)	$V_{DS}=80V$, $V_{GS}=10V$, $I_D=1A$	---	9.7	---	nC
Q_{gs}	Gate-Source Charge		---	1.6	---	
Q_{gd}	Gate-Drain Charge		---	1.7	---	
$T_{d(on)}$	Turn-On Delay Time	$V_{DD}=50V$, $V_{GS}=10V$, $R_G=3.3\Omega$ $I_D=1A$	---	1.6	---	ns
T_r	Rise Time		---	19	---	
$T_{d(off)}$	Turn-Off Delay Time		---	13.6	---	
T_f	Fall Time		---	19	---	
C_{iss}	Input Capacitance	$V_{DS}=15V$, $V_{GS}=0V$, $f=1\text{MHz}$	---	508	---	pF
C_{oss}	Output Capacitance		---	29	---	
C_{rss}	Reverse Transfer Capacitance		---	16.4	---	

Diode Characteristics







Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_S	Continuous Source Current ^{1,4}	$V_G=V_D=0V$, Force Current	---	---	2.2	A
V_{SD}	Diode Forward Voltage ²	$V_{GS}=0V$, $I_S=1A$, $T_J=25^\circ\text{C}$	---	---	1.2	V
T_{rr}	Reverse Recovery Time	$I_F=2A$, $dI/dt=100A/\mu s$, $T_J=25^\circ\text{C}$	---	17	---	nS
Q_{rr}	Reverse Recovery Charge		---	14	---	nC

Note :

- 1.The data tested by surface mounted on a 1 inch² FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$
- 3.The power dissipation is limited by 150°C junction temperature
- 4.The data is theoretically the same as I_D and I_{DM} , in real applications , should be limited by total power dissipation.



Typical Characteristics





N-Ch 100V Fast Switching MOSFETs




Fig.7 Capacitance




Fig.8 Safe Operating Area




Fig.9 Normalized Maximum Transient Thermal Impedance




Fig.10 Switching Time Waveform





Fig.11 Gate Charge Waveform



Ordering Information

Part Number	Package code	Packaging
HSK0008	SOT-89	1000/Tape&Reel

SOT-89 Package Outline



SYMBOLS	MILLIMETERS		NCES	
	MIN	MAX	MIN	MAX
A	1.397	1.600	0.055	0.063
b	0.420	0.540	0.017	0.021
b1	0.420	0.540	0.017	0.021
B	2.388	2.591	0.094	0.102
C	3.937	4.242	0.155	0.167
C1	0.787	1.194	0.031	0.047
D	4.394	4.597	0.173	0.181
D1	1.397	1.753	0.055	0.069
e	1.448	1.549	0.057	0.061
H	0.350	0.44	0.014	0.017



HSK0008 Marking:

