



1. Configuration & Dimensions: (Unit:mm)



SYMBOL	A	B	C	D	E	F	Q'Ty/ Disc
ADT6826	25.0Max	25.0Max	14.0Max	3.5±0.5	9.0±1.0	1.0±0.1	80

2. Electrical Schematics



3. Part Number Code

$\frac{ADT}{A}$ $\frac{6826}{B}$ $\frac{M}{C}$ $\frac{800}{D}$ - $\frac{YP}{E}$

A: Series Name Power Chokes
 B: Dimensions(mm) 6826: 25.0*25.0*14.0 Max
 C: Tolerance M: ±20%
 D: Inductance 800=80uH
 E: Internal controls

4. Electrical Appecification

Part Number	Inductance (uH)	Tolerance	Test Frequency (KHz)	DC Resistance (mΩ) Max.	Heat Rating Current Irms (A)	Current (A)
ADT6826M800-YP	80.0	±20%	1KHz/0.25V	40.0	6.0	15.0