



1. Configuration & Dimensions : (Unit:mm)



SYMBOL	A	B	C	D	E	F	Q'Ty/Box
ADT201208	27.0Max	27.0Max	17.0Max	8.0 ±1.0	12.5Ref	3.0Max	/

2. Electrical Schematics



Winding order	Origination	Parameter
N1	S-F	2UEWΦ1.0mm*2P*14.5TS

3. Part Number Code

ADT 201208 X 401 -WT
 A B C D E

A: Series Name Power Chokes
 B: Dimensions(mm) 201208: 27.0x27.0x17.0 Max
 C: Tolerance X: Min
 D: Inductance 401=400uH
 E: Internal controls

4. Electrical Characteristics

Part Number	Inductance (uH)	Tolerance	Test Frequency (Hz)	DC Resistance (mΩ)Max.	Current (A)Max.
ADT201208X401-WT	400	Min	1KHz/0.25V	21	35

Notes:

- 1) All test data is referenced to 25°C ambient.