

## General Description

The HSH6032 is the high cell density trenched N-ch MOSFETs, which provide excellent R<sub>DS(on)</sub> and gate charge for most of the synchronous buck converter applications.

The HSH6032 meet the RoHS and Green Product requirement, 100% EAS guaranteed with full function reliability approved.


## Features

- Super Low Gate Charge
- 100% EAS Guaranteed
- Green Device Available
- Excellent CdV/dt effect decline
- Advanced high cell density Trench Technology

## Product Summary

V <sub>DS</sub>	60	V
R <sub>DS(ON),typ</sub>	6.5	mΩ
I <sub>D</sub>	90	A

## TO-263 Pin Configuration



## Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V <sub>DS</sub>	Drain-Source Voltage	60	V
V <sub>GS</sub>	Gate-Source Voltage	±20	V
I <sub>D</sub> @T <sub>C</sub> =25°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	90	A
I <sub>D</sub> @T <sub>C</sub> =100°C	Continuous Drain Current, V <sub>GS</sub> @ 10V <sup>1</sup>	58	A
I <sub>DM</sub>	Pulsed Drain Current <sup>2</sup>	360	A
EAS	Single Pulse Avalanche Energy <sup>3</sup>	280	mJ
P <sub>D</sub> @T <sub>C</sub> =25°C	Total Power Dissipation <sup>4</sup>	150	W
T <sub>STG</sub>	Storage Temperature Range	-55 to 150	°C
T <sub>J</sub>	Operating Junction Temperature Range	-55 to 150	°C

## Thermal Data

Symbol	Parameter	Typ.	Max.	Unit
R <sub>θJA</sub>	Thermal Resistance Junction-ambient <sup>1</sup>	---	65	°C/W
R <sub>θJC</sub>	Thermal Resistance Junction-case <sup>1</sup>	---	1.2	°C/W



**Electrical Characteristics (T<sub>J</sub>=25 °C, unless otherwise noted)**

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V , I <sub>D</sub> =250uA	60	---	---	V
R <sub>DS(ON)</sub>	Static Drain-Source On-Resistance <sup>2</sup>	V <sub>GS</sub> =10V , I <sub>D</sub> =20A	---	6.5	8.1	mΩ
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>GS</sub> =V <sub>DS</sub> , I <sub>D</sub> =250uA	2.0	2.8	4.0	V
I <sub>DSS</sub>	Drain-Source Leakage Current	V <sub>DS</sub> =48V , V <sub>GS</sub> =0V , T <sub>J</sub> =25°C	---	---	1	uA
		V <sub>DS</sub> =48V , V <sub>GS</sub> =0V , T <sub>J</sub> =55°C	---	---	5	
I <sub>GSS</sub>	Gate-Source Leakage Current	V <sub>GS</sub> =±20V , V <sub>DS</sub> =0V	---	---	±100	nA
R <sub>g</sub>	Gate Resistance	V <sub>DS</sub> =0V , V <sub>GS</sub> =0V , f=1MHz	---	1.72	---	Ω
Q <sub>g</sub>	Total Gate Charge (10V)	V <sub>DS</sub> =30V , V <sub>GS</sub> =10V , I <sub>D</sub> =18A	---	61	---	nC
Q <sub>gs</sub>	Gate-Source Charge		---	17	---	
Q <sub>gd</sub>	Gate-Drain Charge		---	24	---	
T <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> =30V , V <sub>GS</sub> =10V , R <sub>G</sub> =3.3Ω, I <sub>D</sub> =20A	---	16.2	---	ns
T <sub>r</sub>	Rise Time		---	29.2	---	
T <sub>d(off)</sub>	Turn-Off Delay Time		---	36.4	---	
T <sub>f</sub>	Fall Time		---	2.2	---	
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =30V , V <sub>GS</sub> =0V , f=1MHz	---	3207	---	pF
C <sub>oss</sub>	Output Capacitance		---	211	---	
C <sub>rss</sub>	Reverse Transfer Capacitance		---	181	---	

**Diode Characteristics**


Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I <sub>S</sub>	Continuous Source Current <sup>1,5</sup>	V <sub>G</sub> =V <sub>D</sub> =0V , Force Current	---	---	90	A
V <sub>SD</sub>	Diode Forward Voltage <sup>2</sup>	V <sub>GS</sub> =0V , I <sub>S</sub> =1A , T <sub>J</sub> =25°C	---	---	1.2	V
t <sub>rr</sub>	Reverse Recovery Time	I <sub>F</sub> =20A , dI/dt=100A/μs , T <sub>J</sub> =25°C	---	72	---	nS
Q <sub>rr</sub>	Reverse Recovery Charge		---	42	---	nC

Note :


- 1.The data tested by surface mounted on a 1 inch<sup>2</sup> FR-4 board with 2OZ copper.
- 2.The data tested by pulsed , pulse width ≤ 300us , duty cycle ≤ 2%
- 3.The EAS data shows Max. rating . The test condition is V<sub>DD</sub>=50V,V<sub>GS</sub>=10V,L=0.1mH,I<sub>AS</sub>=40A
- 4.The power dissipation is limited by 150°C junction temperature
- 5.The data is theoretically the same as I<sub>D</sub> and I<sub>DM</sub> , in real applications , should be limited by total power dissipation.




**Typical Characteristics**




**Fig.1 Typical Output Characteristics**




**Fig.2 Transfer Characteristics**




**Fig.3 Power Dissipation**



**Fig.4 Drain Current**




**Fig.5 BV\_DS vs Junction Temperature**




**Fig.6 R\_DS(on) vs Junction Temperature**




**N-Ch 60V Fast Switching MOSFETs**




**Fig.7 Gate Charge Waveforms**



**Fig.8 Capacitance**



**Fig.9 Body Diode Characteristics**



**Fig.10 Maximum Safe Operating Area**



## HSH6032A Marking:

