




Technical Requirements:

- 1,100% continuity testing shall be performed on finished products: no short circuit, open circuit or misconnection is allowed.
- 2,Continuity resistance: 2Ω MAX
- 3,Insulation resistance: 10Ω MIN
- 4,Test voltage: 300VDC
- 5,Products comply with ROHS + REACH standards.

3.0±0.3mm	Plating Sn	P1	Red
3.0±0.3mm	Plating Sn	P2	Yellow
3.0±0.3mm	Plating Sn	P2	White
3.0±0.3mm	Plating Sn	P1	Green
3.0±0.3mm	Plating Sn	P2	Blue
3.0±0.3mm	Plating Sn	P2	Black

Part		ZH1.5-6Y/Plating Sn UL1007-28# L=200mm					
6							
5							
4							
3	Terminal	ZH1.5 Plating Sn				6	pcs
2	Housin	ZH1.5-6Y				1	pcs
1	Wire	UL1007-28AWG R/B wire L=200mm,end plating Sn 3mm	103mm	1.0/3.0T		6	pcs
No.	Material	Description	Cut length of the wires	Set wire stripping length	wire length	QTY	Unit

贝迅泽 BEIXUNZE 贝迅泽技术（东莞）有限公司 BEIXUNZE TECHNOLOGY (DONGGUAN) CO., LTD				
www.hiemi.cn		PN:	ZH1.5-6P-A-200-28A	
Drawn	CHC	Date	2024-11-19	A0
Check	LIKE	Date	2024-11-19	
Approved	WSR	Date	2024-11-19	