




FEATURES

- For general AF applications
- Low collector-emitter saturation voltage
- Complementary types: BC807(PNP)

SOT-23



1.BASE
2.EMITTER
3.COLLECTOR

Classification of h_{FE}

Type	BC817-16	BC817-25	BC817-40
Range	100-250	160-400	250-630
Marking	6A	6B	6C

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS









Absolute Maximum Ratings $T_a = 25^{\circ}\text{C}$

Parameter	Symbol	Rating	Unit
Collector - Base Voltage	V_{CBO}	50	V
Collector - Emitter Voltage	V_{CEO}	45	
Emitter - Base Voltage	V_{EBO}	5	
Collector Current - Continuous	I_C	0.5	A
Collector Power Dissipation	P_C	0.3	W
Junction Temperature	T_J	150	$^{\circ}\text{C}$
Storage Temperature Range	T_{stg}	-55 to 150	

Characteristics ($T_a = 25^\circ\text{C}$)


Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Collector- base breakdown voltage	V_{CBO}	$I_C = 100\ \mu\text{A}, I_E = 0$	50			V
Collector- emitter breakdown voltage	V_{CEO}	$I_C = 10\ \text{mA}, I_B = 0$	45			
Emitter - base breakdown voltage	V_{EBO}	$I_E = 100\ \mu\text{A}, I_C = 0$	5			
Collector-base cut-off current	I_{CBO}	$V_{CB} = 45\ \text{V}, I_E = 0$			0.1	μA
Emitter cut-off current	I_{EBO}	$V_{EB} = 4\ \text{V}, I_C = 0$			0.1	
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = 500\ \text{mA}, I_B = 50\ \text{mA}$			0.7	V
Base - emitter saturation voltage	$V_{BE(sat)}$	$I_C = 500\ \text{mA}, I_B = 50\ \text{mA}$			1.2	
Base - emitter voltage	V_{BE}	$V_{CE} = 1\ \text{V}, I_C = 500\ \text{mA}$			1.2	
DC current gain	$h_{FE(1)}$	$V_{CE} = 1\ \text{V}, I_C = 100\ \text{mA}$	100		630	
	$h_{FE(2)}$	$V_{CE} = 1\ \text{V}, I_C = 500\ \text{mA}$	40			
Collector output capacitance	C_{ob}	$V_{CB} = 10\ \text{V}, f = 1\ \text{MHz}$		10		pF
Transition frequency	f_T	$V_{CE} = 5\ \text{V}, I_C = 10\ \text{mA}, f = 100\ \text{MHz}$	100			MHz

RATING AND CHARACTERISTIC CURVES





Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_P)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C



Package Dimensions & Suggested Pad Layout

SOT23




SOT-23 mechanical data

UNIT	A	C	D	E	H _E	e	M	L	L ₁	a
mm	max	1.1	0.15	1.4	3.0	2.6	0.5	1.95	0.55 (ref)	0.36 (ref)
	min	0.9	0.08	1.2	2.8	2.2	0.3	1.7		0.15
mil	max	43	6	55	118	102	20	77	22 (ref)	14 (ref)
	min	35	3	47	110	87	12	67		6

Dimensions	SOT23
Z	2.9
X	0.8
Y	0.9
C	2.0
E	1.35

Tape & reel specification

Tape



Symbol	Dimension (mm)
P0	4.00±0.10
P1	4.00±0.10
P2	2.00±0.10
D0	1.55±0.10
D1	1.05±0.10
E	1.55±0.10
F	3.60±0.10
W	8.00±0.10
A0	3.80±0.20
B0	3.25±0.20
K0	1.45±0.10
T	0.25±0.05
D2	178.0±3.0
D3	55Min.
D4	R24.0±3.0
G	R82.0±3.0
I	13.0±2.0
W1	11.0±3.0
Quantity: 3000PCS	

7" Reel

