


FEATURES

- Fast Switching Speed
- Surface Mount Package Ideally Suited for Automated Insertion
- For General Purpose Switching Applications
- High Reverse Breakdown Voltage

MECHANICAL DATA

- Package: SOD123FL
- Package Material: Molded Plastic, "Green" Molding Compound.
UL Flammability Classification Rating 94V-0



BAV19WL Marking: A8
BAV20WL Marking: T2
BAV21WL Marking: T3

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.
Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

TYPE NUMBER	BAV19WL	BAV20WL	BAV21WL	UNITS
Maximum Recurrent Peak Reverse Voltage	120	200	250	V
Maximum RMS Voltage	100	150	200	V
Maximum DC Blocking Voltage	120	200	250	V
Maximum Average Forward Rectified Current	0.25			A
Peak Forward Surge Current	1.0			A
@ at 1s	3.0			A
@ at 1ms	9.0			A
@ at 1 us	1.25			V
Maximum Instantaneous Forward Voltage at 0.2A	1.25			V
Maximum DC Reverse Current	0.1			μA
at Rated DC Blocking Voltage	Ta=25°C			
Typical Junction Capacitance	3.5			pF
Total Power Dissipation	250			mW
Maximum Reverse Recovery Time	50			ns
Operating Temperature Range T _J	-55 to +150			°C
Storage Temperature Range T _{STG}	-55 to +150			°C

RATING AND CHARACTERISTIC CURVES

FIG.1-TYPICAL Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics




Fig. 3 Typical Reverse Characteristics




Fig. 4 Total Capacitance vs. Reverse Voltage






Fig. 5 Maximum Non-Repetitive Surge Currer




Soldering parameters

Reflow Condition		Pb-Free assembly (see as below)
Pre Heat	-Temperature Min ($T_{s(min)}$)	+150°C
	-Temperature Max($T_{s(max)}$)	+200°C
	-Time (Min to Max) (ts)	60-180 secs.
Average ramp up rate (Liquid us Temp (T_L) to peak)		3°C/sec. Max
$T_{s(max)}$ to T_L - Ramp-up Rate		3°C/sec. Max
Reflow	-Temperature(T_L)(Liquid us)	+217°C
	-Temperature(t_L)	60-150 secs.
Peak Temp (T_P)		+260(+0/-5)°C
Time within 5°C of actual Peak Temp (t_p)		30 secs. Max
Ramp-down Rate		6°C/sec. Max
Time 25°C to Peak Temp (T_P)		8 min. Max
Do not exceed		+260°C




Package Dimensions & Suggested Pad Layout

SOD123FL





SOD123FL		
Dim	Min	Max
A	1.00	1.20
b	0.80	1.10
c	0.12	0.20
D	1.75	1.95
E	2.60	2.90
He	3.55	3.80
L2	0.50	0.85
All Dimensions in mm		



Dimensions	Value (in mm)
C	3.25
G	2.00
X	1.25
X1	4.50
Y	1.50

Tape & reel specification

Tape		Symbol	Dimension (mm)
 SECTION : A-A SECTION : B-B		P0	4.00±0.20
		P1	4.00±0.20
		P2	2.00±0.20
		D0	1.55±0.15
		D1	1.00±0.20
		E	1.75±0.20
		F	3.50±0.25
		W	8.00±0.20
		A0	1.85±0.20
		B0	3.95±0.20
		K0	1.30±0.20
		T	0.21±0.10
7" Reel			
		D2	178.0±5.0
		D3	55.0Min.
		D4	10.0±2.5
		W1	11.5±2.5
		Quantity: 3000PCS	