


1. Description

The ADM232A have two drives and two receivers. The drivers and receivers meet all EIA/TIA-232E and CCITT V.28 specifications at data rates up to 200kB/s when loaded in accordance with the EIA/TIA-232E specification

2. Features


- Operate from Single +5 V Power Supply
- Guaranteed 200kB/ Data Rate
- Latchup Free
- ESD Protection $\pm 2kV$

3. Typical Operating Circuit





4. Pinning Information



SOP-16

| Pin No | Symbol | Function |
|--------|-------------------|---|
| 01 | C1+ | Terminal for positive charge-pump capacitor |
| 02 | V+ | +2 V _{CC} voltage generated by the charge-pump |
| 03 | C1- | Terminal for positive charge-pump capacitor |
| 04 | C2+ | Terminal for negative charge-pump capacitor |
| 05 | C2- | Terminal for negative charge-pump capacitor |
| 06 | V- | -2 V _{CC} voltage generated by the charge-pump |
| 07 | T2 _{OUT} | RS-232 Driver Output |
| 08 | R2 _{IN} | RS-232 Receiver Input |
| 09 | R2 _{OUT} | RS-232 Receiver Output |
| 10 | T2 _{IN} | RS-232 Driver Input |
| 11 | T1 _{IN} | RS-232 Driver Input |
| 12 | R1 _{OUT} | RS-232 Receiver Output |
| 13 | R1 _{IN} | RS-232 Receiver Input |
| 14 | T1 _{OUT} | RS-232 Driver Output |
| 15 | GND | Ground |
| 16 | V _{CC} | + 4.5 V to 5.5 V Supply Voltage Input |



5. Absolute Maximum Ratings

| Parameter | Symbol | Min | Max | Units |
|--|------------|--------------|--------------|-------|
| Supply voltage | V_{CC} | -0.3 | 6 | V |
| Transmitter high output voltage | V_{+} | $V_{CC}-0.3$ | 13 | |
| Transmitter low output voltage | V_{-} | -13 | +0.3 | |
| Transmitter input voltage | V_{TIN} | -0.3 | $V_{CC}+0.3$ | |
| Receiver input voltage | V_{RIN} | -30 | 30 | |
| Output voltages (transmitters) | V_{TOUT} | $V_{-}-0.3$ | $V_{+}+0.3$ | |
| Output voltages (receivers) | V_{ROUT} | -0.3 | $V_{CC}+0.3$ | |
| Power dissipation | P_D | | 842 | mW |
| So-package (derate 9.52 mW/C above 70°C) | | | 400 | |
| Short-Circuit Duration (T_{OUT}) | I_{SC} | | Continuous | |
| Storage temperature | T_{STG} | -60 | 150 | °C |
| Operating voltage range | T_A | -40 | 85 | °C |



6. Electrical Characteristics

$V_{CC}=4.5V$ to $5.5V$, $C1-C4 = 0.1\mu F$; $T_A = -40$ to $+85^\circ C$ unless otherwise noted)

| Parameter | Symbol | Conditions | Min | Max | Units |
|--------------------------------|--------------|--|---------|----------|------------|
| DC CHARACTERISTICS | | | | | |
| Operating Voltage Range | V_{CC} | $V_{IL}=0V$ | 4.5 | 5.5 | V |
| V_{CC} Supply Current | I_{CC} | No load, $T_A = 25^\circ C$ | | 10 | mA |
| LOGIC | | | | | |
| Input Leakage Current | I_i | $T_{IN}=0V$ to V_{CC} | 0.2 | ± 10 | μA |
| Input Threshold Low | V_{IL} | T_{IN} | | 0.8 | V |
| Input Threshold High | V_{IH} | T_{IN} | 2 | | V |
| Output Voltage Low | V_{OL} | R_{OUT} , $I_{OUT}=3.2mA$ | | 0.4 | V |
| Output Voltage High | V_{OH} | R_{OUT} , $I_{OUT}=-1mA$ | 3.5 | | V |
| RECEIVER INPUTS | | | | | |
| Input Voltage Range | V_{RIN} | All parts, normal operation | -30 | 30 | V |
| Input Threshold Low | V_{ff} | $T_A=+25^\circ C$, $V_{CC}=5V$ | 0.8 | | V |
| Input Threshold High | I_{on} | $T_A=+25^\circ C$, $V_{CC}=5V$ | | 2.4 | V |
| Input Hysteresis | V_h | $V_{CC}=5V$ | 0.2 | 1 | V |
| Input Resistance | R_i | $T_A=+25^\circ C$, $V_{CC}=5V$ | 3 | 7 | k Ω |
| TRANSMITTER OUTPUTS | | | | | |
| Output Voltage Swing | ΔV_O | All driver inputs loaded with 3k Ω to ground | ± 5 | | V |
| Output resistance | R_O | $V_{CC}=V+=V-=0V$, $V_{OUT}=+2V$ | 300 | | Ω |
| Output Short - Circuit Current | I_{SC} | | | ± 60 | mA |



| Parameter | Symbol | Conditions | Min | Max | Units |
|-------------------------------|--------------------------|--|-----|-----|------------|
| TIMING CHARACTERISTICS | | | | | |
| Maximum Data Rate | ST | $R_L=3k\Omega$ to 7 k Ω $C_L=50pF$ to 1000pF onetransmitter switcing | 200 | | kB/s |
| Reseiver Propagation Delay | t_{PLHR} t_{PHLR} | $C_L=150pF$ All parts, normal operation(Fig. 1) | | 10 | μS |
| Transmitter Propagation Delay | t_{PLHT} t_{PHLT} | $R_L=3k\Omega$, $C_L=2500pF$ all transmitters loaded (Fig.2) | | 6 | μS |
| Transition-Region Slew Rate | SR | $T_A=25^\circ C$, $V_{CC}=5V$ $R_L=3k\Omega$ to 7 k Ω $C_L=50pF$ to 2500pF measured from $-3V$ to +3V or +3V to -3V(Fig.3) | 3 | 30 | V/ μS |



7. Timing Diagram




Figure 1




Figure 2





Figure 3



8.SOP-16 Package Outline Dimensions




DIMENSIONS (mm are the original dimensions)

| Symbol | A | A1 | A2 | b | c | D | E | E1 | e | L | θ |
|--------|-------|-------|-------|-------|-------|--------|-------|-------|-------|-------|----------|
| Min | 1.350 | 0 | 1.350 | 0.330 | 0.170 | 9.800 | 3.800 | 5.800 | 1.270 | 0.400 | 0° |
| Max | 1.750 | 0.100 | 1.550 | 0.510 | 0.250 | 10.200 | 4.000 | 6.200 | BSC | 1.270 | 8° |



9. Ordering information



yy: Year Code
ww: Week Code

| Order Code | Package | Base QTY | Delivery Mode |
|-----------------|---------|----------|---------------|
| UMW ADM232AARNZ | SOP-16 | 2500 | Tape and reel |



10. Disclaimer

UMW reserves the right to make changes to all products, specifications. Customers should obtain the latest version of product documentation and verify the completeness and currency of the information before placing an order.

When applying our products, please do not exceed the maximum rated values, as this may affect the reliability of the entire system. Under certain conditions, any semiconductor product may experience faults or failures. Buyers are responsible for adhering to safety standards and implementing safety measures during system design, prototyping, and manufacturing when using our products to prevent potential failure risks that could lead to personal injury or property damage.

Unless explicitly stated in writing, UMW products are not intended for use in medical, life-saving, or life-sustaining applications, nor for any other applications where product failure could result in personal injury or death. If customers use or sell the product for such applications without explicit authorization, they assume all associated risks.

When reselling, applying, or exporting, please comply with export control laws and regulations of China, the United States, the United Kingdom, the European Union, and other relevant countries, regions, and international organizations.

This document and any actions by UMW do not grant any intellectual property rights, whether express or implied, by estoppel or otherwise. The product names and marks mentioned herein may be trademarks of their respective owners.