



◆ Features:

- ◇ Fast switching speed
开关速度快
- ◇ Low gate charge
低门充电
- ◇ High power and current handling capability
高功率和电流处理能力
- ◇ ROHS compliant
符合 ROHS 标准

◆ Applications

- ◇ DC to DC converters
直流到直流转换
- ◇ Synchronous Rectification
同步整流



单位: mm
TO-220F

◆ Absolute Maximum Ratings (Tc=25°C)

Symbol	Parameters	Ratings	Unit
V _{DSS}	Drain-Source Voltage 漏源电压	40	V
V _{GS}	Gate-Source Voltage-Continuous 栅源电压	±20	V
I _D	Drain Current-Continuous (Note 2) 漏极持续电流	130	A
I _{DM}	Drain Current-Single Plused (Note 1) 漏极单次脉冲电流	480	A
P _D	Power Dissipation (Note 2) 功率损耗	66	W
T _j	Max.Operating junction temperature 最大结温	150	°C

◆ Electrical characteristics (Tc=25°C unless otherwise noted)

Symbol	Parameters	Min	Typ	Max	Units	Conditions
Static Characteristics						
B _{VDSS}	Drain-Source Breakdown Voltage Current (Note 1) 漏极击穿电压	40	--	--	V	I _D =250μA, V _{GS} =0V
V _{GS(th)}	Gate Threshold Voltage 栅极开启电压	1.0	--	2.5	V	V _{DS} =V _{GS} , I _D =250μA
R _{DS(on)}	Drain-Source On-Resistance 漏源导通电阻	--	3.0	3.5	mΩ	V _{GS} =10V, I _D =20A
I _{GSS}	Gate-Body Leakage Current 栅极漏电流	--	--	±100	nA	V _{GS} =±20V, V _{DS} =0
I _{DSS}	Zero Gate Voltage Drain Current 零栅极电压漏极电流	--	--	1	μA	V _{DS} =40V, V _{GS} =0
g _{fs}	Forward Trans conductance 正向跨导	--	50	--	S	V _{DS} =5V, I _D =20A



OSPF120N04T

LOW Voltage N-Channel MOSFET

Switching Characteristics						
$T_{d(on)}$	Turn-On Delay Time 开启延迟时间	--	17	--	ns	$V_{GS}=10V,$ $V_{DS}=20V, I_D=15A,$ $R_G=4.5\Omega$
T_r	Rise Time 上升时间	--	18	--	ns	
$T_{d(off)}$	Turn-Off Delay Time 关闭延迟时间	--	48	--	ns	
T_f	Fall Time 下降时间	--	18	--	ns	
Q_g	Total Gate Charge 栅极总电荷	--	125	--	nC	$V_{DS}=15V,$ $V_{GS}=10V,$ $I_D=25A$
Q_{gs}	Gate-Source Charge 栅源极电荷	--	25	--	nC	
Q_{gd}	Gate-Drain Charge 栅漏极电荷	--	11	--	nC	
Dynamic Characteristics						
C_{iss}	Input Capacitance 输入电容	--	7500	--	pF	$V_{DS}=25V, V_{GS}=0,$ $f=1MHz$
C_{oss}	Output Capacitance 输出电容	--	530	--	pF	
C_{rss}	Reverse Transfer Capacitance 反向传输电容	--	520	--	pF	
I_S	Continuous Drain-Source Diode Forward Current (Note 2) 二极管导通正向持续电流	--	--	120	A	
V_{SD}	Diode Forward On-Voltage 二极管正向导通电压	--	--	1.2	V	$I_S=20A, V_{GS}=0$
$R_{th(j-c)}$	Thermal Resistance, Junction to Case 结到外壳的热阻	--	--	1.89	$^{\circ}C/W$	

Note 1: Repetitive Rating : Pulse width limited by maximum junction temperature

Note 2: Pulse test: PW \leq 300us , duty cycle \leq 2%.