

## Product Summary

$V_{(BR)DSS}$	$R_{DS(on)TYP}$	$I_D$
100V	1.05mΩ@10V	390A




## Feature

- Fast Switching
- Low Gate Charge and Rdson
- 175°C Junction Temperature
- Advanced Split Gate Trench Technology
- 100% Single Pulse avalanche energy Test

## Applications


- DC-DC Converters
- Power management functions
- Synchronous-rectification applications

## Package



TOLL

## Circuit diagram



## Marking



SP010N01BGHTOA  
\*\*

=Device Code  
=Week Code

## Order Information

Device	Package	Unit/Tape
SP010N01BGHTOA	TOLL	2000

**Absolute maximum ratings (Ta=25°C, unless otherwise noted)**

Parameter	Symbol	Rating	Unit
Drain-Source Voltage	$V_{DSS}$	100	V
Gate-Source Voltage	$V_{GSS}$	$\pm 20$	V
Continuous Drain Current (Tc=25°C)	$I_D$	390	A
Continuous Drain Current (Tc=100°C)	$I_D$	262	A
Pulse Drain Current Tested	$I_{DM}$	1560	A
Single pulsed avalanche energy <sup>1</sup>	$E_{AS}$	2205	mJ
Power Dissipation (Tc=25°C)	$P_D$	430	W
Power Dissipation (Tc=100°C)	$P_D$	215	W
Thermal Resistance Junction-to-Case	$R_{\theta JC}$	0.35	°C/W
Thermal Resistance Junction-to-Ambient	$R_{\theta JA}$	44	°C/W
Storage Temperature Range	$T_{STG}$	-55 to 175	°C
Operating Junction Temperature Range	$T_J$	-55 to 175	°C


**Electrical characteristics (Ta=25°C, unless otherwise noted)**

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
<b>Static Characteristics</b>						
Drain-Source Breakdown Voltage	$BV_{DSS}$	$V_{GS}=0V, I_D=250\mu A$	105	110	-	V
Drain-Source Leakage Current	$I_{DSS}$	$V_{DS}=100V, V_{GS}=0V, T_J=25^\circ C$	-	-	1	$\mu A$
Gate-Source Leakage Current	$I_{GSS}$	$V_{GS}=\pm 20V, V_{DS}=0V$	-	-	$\pm 100$	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS}=V_{DS}, I_D=250\mu A$	2.5	3.0	3.5	V
Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=50A$	-	1.05	1.15	m $\Omega$
Gate Resistance	$R_G$	$V_{DS}=50V, V_{GS}=0V, f=1MHz$	-	3.9	-	$\Omega$
<b>Dynamic characteristics</b>						
Input Capacitance	$C_{iss}$	$V_{DS}=50V, V_{GS}=0V, f=1MHz$	-	11787	-	pF
Output Capacitance	$C_{oss}$		-	2160	-	
Reverse Transfer Capacitance	$C_{rss}$		-	46	-	
Total Gate Charge	$Q_g$	$V_{DS}=50V, V_{GS}=10V, I_D=125A$	-	212	-	nC
Gate-Source Charge	$Q_{gs}$		-	63	-	
Gate-Drain Charge	$Q_{gd}$		-	55	-	
Gate Plateau Voltage	$V_{plateau}$		-	4.7	-	
<b>Switching Characteristics</b>						
Turn-On Delay Time	$t_{d(on)}$	$V_{DD}=50V, V_{GS}=10V, R_G=1.6\Omega, I_D=125A$	-	41	-	nS
Rise Time	$t_r$		-	67	-	
Turn-Off Delay Time	$t_{d(off)}$		-	143	-	
Fall Time	$t_f$		-	86	-	
<b>Diode Characteristics</b>						
Diode Forward Voltage	$V_{SD}$	$V_{GS}=0V, I_S=1A, T_J=25^\circ C$	-	-	1.2	V
Diode Continuous Current	$I_S$		-	-	390	A
Reverse recover time	$T_{rr}$	$I_S=20A, di/dt=100A/\mu s, T_J=25^\circ C$	-	132	-	nS
Reverse recovery charge	$Q_{rr}$		-	364	-	nC


**Note :**

- The test condition is  $V_{DD}=50V, V_{GS}=10V, L=0.5mH, R_G=25\Omega$


**Typical Characteristics**




Output Characteristics




Typical Transfer Characteristics




On-resistance vs. Drain Current









Body Diode Characteristics




$R_{DS(ON)}$  vs.  $V_{GS}$





Capacitance Characteristics







## Test Circuit



### Gate Charge





### Resistive Load Switching Time




### Un-clamped Inductive Load Switching



### Drain-Source Body Diode Reverse Recovery



**Temperature Profile for IR Reflow Soldering**



Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
<b>Preheat &amp; Soak</b>		
Temperature min (T <sub>smin</sub> )	100°C	150°C
Temperature max (T <sub>smax</sub> )	150°C	200°C
Time (T <sub>smin</sub> to T <sub>smax</sub> ) (t <sub>s</sub> )	60-120 seconds	60-120 seconds
Average ramp-up rate (T <sub>smax</sub> to T <sub>p</sub> )	3 °C/second max.	3°C/second max.
Liquidous temperature (T <sub>L</sub> )	183 °C	217°C
Time at liquidous (t <sub>L</sub> )	60-150 seconds	60-150 seconds
Peak package body Temperature e (T <sub>p</sub> )*	See Classification Temp in table 1	See Classification Temp in table 2
Time (t <sub>p</sub> )** within 5°C of the specified classification temperature (T <sub>c</sub> )	20** seconds	30** seconds
Average ramp-down rate (T <sub>p</sub> to T <sub>smax</sub> )	6 °C/second max.	6 °C/second max.
Time 25°C to peak temperature	6 minutes max.	8 minutes max.
* Tolerance for peak profile Temperature (T <sub>p</sub> ) is defined as a supplier minimum and a user maximum. ** Tolerance for time at peak profile temperature (t <sub>p</sub> ) is defined as a supplier minimum and a user maximum		

Table 1. SnPb Eutectic Process – Classification Temperatures (T<sub>c</sub>)



Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2. Pb-free Process – Classification Temperatures (T<sub>c</sub>)


Package Thickness	Volume mm <sup>3</sup> <350	Volume mm <sup>3</sup> 350-2000	Volume mm <sup>3</sup> >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 mm – 2.5 mm	260 °C	250 °C	245 °C
≥2.5 mm	250 °C	245 °C	245 °C

### TOLL Reel Information

REEL DIMENSIONS



TAPE DIMENSIONS




- A0: Dimension designed to accommodate the component width
- B0: Dimension designed to accommodate the component length
- K0: Dimension designed to accommodate the component thickness
- W: Overall width of the carrier tape
- P0: Pitch between successive cavity centers and sprocket hole
- P1: Pitch between successive cavity centers
- P2: Pitch between sprocket hole
- T: Tape material thickness
- D1: Reel Diameter
- W1: Reel Width

DIMENSIONS										(Unit: mm)
Reel	D1	W1								Material
	330	24.4								Hips
Tape	P0	P1	P2	W	A0	B0	K0	T	Pin 1 Quadrant	Material
	2	4	12	24	10.3	12.1	2.6	0.35	Q1	PC

All dimensions are nominal

## TOLL Package Outline Dimensions



- NOTES: 1.PKG SURFACE Ra=1.40±0.20um.  
 2.EJECTION MARK DEPTH 0.10±0.10mm.  
 3.L/F THICKNESS AFTER PLATING 0.50±0.02mm.  
 4.ALL DIMENSIONS IN MILLIMETERS.

Symbol	Dimensions In Millimeters		
	Min.	Nom.	Max.
A	2.20	2.30	2.40
b	0.60	0.70	0.80
b1	1.10	1.20	1.30
b2	0.36 REF.		
C	0.40	0.50	0.60
D	10.30	10.40	10.50
D1	3.20	3.30	3.40
D2	4.08	4.18	4.28
D3	0.53	0.63	0.73
D4	7.35 REF.		
E	9.80	9.9	10.00
E1	9.70	9.80	9.90
E2	8.80 REF.		
E3	8.95 REF.		
e	1.20 BSC.		
H	11.5	11.7	11.90
L	0.5	0.6	0.7
L1	0.60	0.7	0.80
L2	0.10 REF.		
L3	1.27 REF.		
L4	1.10 REF.		
P	2.00	3.00	4.00
R	3.00	3.10	3.20
θ	7°	9°	11°
θ1	3°	5°	7°