




Technical Requirements:

1,100% continuity testing shall be performed on finished products: no short circuit, open circuit or misconnection is allowed.

2,Continuity resistance: 2Ω MAX

3,Insulation resistance: 10Ω MIN

4,Test voltage: 300VDC

5,Products comply with ROHS + REACH standards.

P2

Plating Sn

P1

PH2.0-2Y

3.0±0.3mm

Plating Sn

P1

Red

3.0±0.3mm

Plating Sn

P2

Black

Part		PH2.0-2Y/ plating Sn UL1007-26# L=300mm					
6							
5							
4							
3	Terminal	PH2.0 Plating Sn				2	pcs
2	Housing	PH2.0-2Y White				1	pcs
1	Wire	UL1007-26AWG R/B wire L=300mm,end plating Sn 3mm	103mm	1.0/3.0T		2	pcs
No.	Material	Description	Cut length of the wires	Set wire stripping length	wire length	QTY	Unit



贝迅泽技术（东莞）有限公司
BEIXUNZE TECHNOLOGY (DONGGUAN) CO., LTD

www.hiemi.cn

PN:

PH2.0-2P-A-300-26A

Drawn

CHC

Date

2024-11-19

A0

Check

LIKE

Date

2024-11-19

Approved

WSR

Date

2024-11-19