







SPECIFICATIONS
Current Rating: 3Amps
Insulation Resistance: 1000M Ω Min
Contact Resistance: 20M Ω Max
Withstanding Voltage: AC 1000V
Operation Temperature: -40° to +105°
Contact Material: Copper Alloy
Standard: PA6T
Insulator Material: Polyester (UL 94V-0)
Contact Plating: Gold Flash
Max. Processing Temp: 240°C for 30-60 seconds
(260°C for 5 seconds)



P/N	PIN	DIM.A	DIM.B
PH2.54-01-01PZS	2*1	0.00	2.54
PH2.54-01-02PZS	2*2	2.54	5.08
PH2.54-01-03PZS	2*3	5.08	7.62
PH2.54-01-04PZS	2*4	7.62	10.16
PH2.54-01-05PZS	2*5	10.16	12.70
PH2.54-01-06PZS	2*6	12.70	15.24
PH2.54-01-07PZS	2*7	15.24	17.78
PH2.54-01-08PZS	2*8	17.78	20.32
PH2.54-01-09PZS	2*9	20.32	22.86
.....			
PH2.54-01-40PZS	2*40	(PIN-1)X2.54	(PIN)X2.54

PART NUMBER DESCRIPTION:

PH2.54-01-NPZS

(D=单排; S=双排)
(Z=直脚; W=弯脚)
(PIN数量; 01.....40PIN)
(排针开关)

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co., Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: 2.54PH H2.5 2xNPIN 180度 PC3.0 PA6.0 PB2.5 L11.5 6T
			PAR PH2.54-01-NPZS
DECIMALS:	ANGLES:		DWN
X. ± 0.30	X° $\pm 5'$		CHKD
X.X ± 0.20	X.X° $\pm 1'$	CUSTOMER COPY	APVD
X.XX ± 0.10	X.XX° $\pm 0.5'$		SCALE N:A
		UNIT:MM	UNIT:MM
		SIZE:A4	SHEET:1F1
		REV:A	REV:A