HBSS131H6327XTSA1

N-Channel Enhancement Mode MOSFET

Description

The HBSS131H6327XTSA1 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.

SOT-23



N-Channel MOSFET

General Features

V_{DS} = 240V I_D =0.1A

$R_{DS(ON)}$ < 5Ω@ V_{GS}=10V

Application

Battery protection

Load switch

Uninterruptible power supply

Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
HBSS131H6327XTSA1	SOT-23	SR	3000

Absolute Maximum Ratings (T_C=25°C unless otherwise noted)

Symbol	Parameter		Limit	Unit
V_{DS}	Drain-Source Voltage		240	V
V_{GS}	Gate-Source Voltage		±20	V
I_D	Continuous Drain Current (T_J =150°C)	T_A =25°C	0.1	A
		T_A =100°C	0.09	
I_{DM}	Drain Current-Pulsed		0.4	A
P_D	Maximum Power Dissipation		0.36	W
T_J,T_{STG}	Operating Junction and Storage Temperature Range		-55 To 150	℃
$R_{\theta JA}$	Thermal Resistance,Junction-to-Ambient		200	℃/W

Electrical Characteristics (T_A=25℃unless otherwise noted)

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Thermal resistance, junction - minimal footprint	R_{thJA}		-	-	350	K/W
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0 V, I_D=250 µA	240	-	-	V
Gate threshold voltage	$V_{GS(th)}$	V_{DS}=0 V, I_D=56 µA	0.8	1.4	1.8	
Drain-source leakage current	$I_{D\ (off)}$	V_{DS}=240 V, V_{GS}=0 V, T_j=25 °C	-	-	0.01	µA
		V_{DS}=240 V, V_{GS}=0 V, T_j=150 °C	-	-	5	
Gate-source leakage current	I_{GSS}	V_{GS}=20 V, V_{DS}=0 V	-	-	10	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=4.5 V, I_D=0.09 A	-	6	10	Ω
		V_{GS}=10 V, I_D=0.1 A	-	3	5	
Transconductance	g_{fs}	$\|V_{DS}\|>2\|I_D\|R_{DS(on)max}$, I_D=0.08 A	0.06	0.13	-	S
Input capacitance	C_{iss}	V_{GS}=0 V, V_{DS}=25 V, f=1 MHz	-	58	77	pF
Output capacitance	C_{oss}		-	7.3	10	
Reverse transfer capacitance	C_{rss}		-	2.8	4.2	
Turn-on delay time	$t_{d(on)}$	V_{DD}=120 V, V_{GS}=10 V, I_D=0.1 A, R_G=6 Ω	-	3.3	5.0	ns
Rise time	t_r		-	3.1	4.6	
Turn-off delay time	$t_{d(off)}$		-	13.7	20	
Fall time	t_f		-	64.5	97	
Gate to source charge	Q_{gs}	V_{DD}=192 V, I_D=0.1 A, V_{GS}=0 to 10 V	-	0.16	0.22	nC
Gate to drain charge	Q_{gd}		-	0.8	1.2	
Gate charge total	Q_g		-	2.1	3.1	
Gate plateau voltage	$V_{plateau}$		-	2.90	-	V
Diode continous forward current	I_S	T_A=25 °C	-	-	0.11	A
Diode pulse current	$I_{S,pulse}$		-	-	0.43	
Diode forward voltage	V_{SD}	V_{GS}=0 V, I_F=0.1 A, T_j=25 °C	-	0.81	1.2	V
Reverse recovery time	t_{rr}	V_R=120 V, I_F=0.1 A, di_F/dt=100 A/µs	-	42.9	64.3	ns
Reverse recovery charge	Q_{rr}		-	22.6	34	nC

Typical Characteristics

1 Power dissipation

$P_{tot}=f(T_A)$



2 Drain current

$I_D=f(T_A)$; $V_{GS}\geq 10$ V



3 Safe operating area

$I_D=f(V_{DS})$; $T_A=25$ °C; $D=0$

parameter: t_p



4 Max. transient thermal impedance

$Z_{thJA}=f(t_p)$

parameter: $D=t_p/T$



5 Typ. output characteristics

I_D=f(V_{DS}); T_j=25 °C

parameter: V_{GS}



6 Typ. drain-source on resistance

$R_{DS(on)}$=f(I_D); T_j=25 °C

parameter: V_{GS}



7 Typ. transfer characteristics

I_D=f(V_{GS}); |V_{DS}|>2|I_D|$R_{DS(on)max}$



8 Typ. forward transconductance

g_{fs}=f(I_D); T_j=25 °C



9 Drain-source on-state resistance

$R_{DS(on)}$=f(T_j); I_D=0.1 A; V_{GS}=10 V



10 Typ. gate threshold voltage

$V_{GS(th)}$=f(T_j); V_{DS}=V_{GS}; I_D=56 µA

parameter: I_D



11 Typ. capacitances

C=f(V_{DS}); V_{GS}=0 V; f=1 MHz; T_j=25°C



12 Forward characteristics of reverse diode

I_F=f(V_{SD})

parameter: T_j



13 Typ. gate charge

V_{GS}=f(Q_{gate}); I_D=0.1 A pulsed

parameter: V_{DD}



14 Drain-source breakdown voltage

$V_{BR(DSS)}$=f(T_j); I_D=250 µA



SOT-23 Package Outline Dimensions



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	0.900	1.150	0.035	0.045
A1	0.000	0.100	0.000	0.004
A2	0.900	1.050	0.035	0.041
b	0.300	0.500	0.012	0.020
c	0.080	0.150	0.003	0.006
D	2.800	3.000	0.110	0.118
E	1.200	1.400	0.047	0.055
E1	2.250	2.550	0.089	0.100
e	0.950 TYP		0.037 TYP	
e1	1.800	2.000	0.071	0.079
L	0.550 REF		0.022 REF	
L1	0.300	0.500	0.012	0.020
θ	0°	8°	0°	8°

SOT-23 Suggested Pad Layout



Note:
1.Controlling dimension:in millimeters.
2.General tolerance:± 0.05mm.
3.The pad layout is for reference purposes only.

Attention

■ Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.

■ HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.

■ Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.

■ HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could
give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.

■ In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.

■ No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.

■ Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.

■ Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.