



Datasheet

RS Pro Extra Thin Cutting Disc - Metal/INOX - 125 × 1.0 × 22.23mm - 12,200rpm

RS Stock No: **184-9242**



Product Details

RS Pro Extra Thin Cutting Disc is produced to O.S.A Safety Standards. Extremely fast and precise cutting with minimal effort required. Designed for use on a range of material applications including stainless steel, mild steel, hardened steel and high grade steel, with strengthened core stability for reduced vibration. These discs do not contain iron, sulphur or chlorine.

Features and Benefits

- 12,200rpm maximum safe speed
- Free from iron, sulphur and chlorine
- Professional quality at an affordable price
- Straight fast cutting action
- Reduced Vibration
- Manufactured to O.S.A Safety Standards

Specifications:

Abrasive Material	Aluminium Oxide
Grade	20A46RBF
Bore Size	22.23mm
Disc Diameter	125mm
Grit Size	60
Maximum Safe Speed	12,200rpm
Thickness	1mm
Number of Pieces	5
Suitable for	Steel & Stainless Steel

RS, Professionally Approved Products, gives you professional quality parts across all products categories. Our range has been testified by engineers as giving comparable quality to that of the leading brands without paying a premium price.