


HX-series



■ Feature

Meets IEEE 802.3 and ANSIX3.263 standards .RoHS Compliant
10/100/1000 Base-T,Surface Mount Type,Open Header
Cable interface for isolation and low common mode emissions.
Reflow soldering temperature: peak temperature $\leq 250\text{ }^{\circ}\text{C}$ (10s)
Reflow soldering frequency: It is recommended not to exceed 3 times
Storage temperature range: -55°C to $+125^{\circ}\text{C}$
Operating temperature range: -40°C to $+85^{\circ}\text{C}$

■ ROHS REACH marking


■ CE FCC marking



2 Specifications

Part No	OCL(uH min) @100KHz/0.1Vrms 8MA DC BIAS	Turns Ratio(3%)	Leakage primary@10KHz 0.1Vrms	DCR (Ω) Max	Cww(Pri:Sec) pF Typ	Isolation Voltage(AC Vrms 1S)	
HX5084NLT	350UH	1:1	0.5uH max	0.9/1.2	35	1500V	
Part No	Insertion loss (dB max) 1-100MHz	Return Loss(dB Min)MHz			DMRR(dB min)MHz		Crosstalk(dB min)MHz
		1-30	40~60	60~100	1-60	60~100	1~100
HX5084NLT	-1.2	-18	-16	-14	-40	-30	-35


3 Mechanical




Suggested PAD Layout

※unit: mm

4 Schematic



5 packing



※unit: mm

※ Packaging quantity : * 800pcs/roll * 6400pcs/box

※ Outer box size: * L * * W * * H