

特点

- 提供各种螺纹尺寸
- 坚固的镀锌钢
- 头高度等于柄直径
- 经济实惠

RS M3 Pro 6mm 内六角半圆头 螺钉、采用亮光 镀锌钢

RS 号: 822-9155



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与领先品牌相当的质量、而无需支付高昂的价格。

商品描述属性

RS Pro 系列半圆头凹头螺钉提供的出色功能、适用于机器维修和固定应用。这些双镀锌钢是其他昂贵不锈钢的经济型解决方案、具有出色的固定方法。如果不存在腐蚀问题、它们特别适用于室内应用。所有型号均高度可靠且质量极佳。

一般规格

螺纹尺寸	M3
头部形状	六角套筒按钮
材料	钢
表面	亮镀锌
螺纹类型	公制
等级	10.9
应用	木材加工、家用应用、紧固件和固定件、机器工具和维修、安全防护、面板制造

机械规格

长度	6mm
螺距	0.5mm
头直径范围	5.4mm 至 5.7mm
头部高度范围	1.40mm 至 1.65mm
钥匙尺寸标称范围	2.020mm 至 2.045mm
关键敬业度	1.04
螺纹公差	6g

认证

合规性 / 认证

rohs 符合性证书, ISO7380, ansi B18




Please view our full range listing below for all BZP Steel Hexagon Socket Button Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Socket Button	Steel BZP	M3	6 mm	8229155
Socket Button	Steel BZP	M4	6 mm	8229164
Socket Button	Steel BZP	M4	20 mm	8229167
Socket Button	Steel BZP	M4	25 mm	8229161
Socket Button	Steel BZP	M5	6 mm	8229170
Socket Button	Steel BZP	M5	8 mm	8229173
Socket Button	Steel BZP	M5	25 mm	8229177
Socket Button	Steel BZP	M5	35 mm	8229186
Socket Button	Steel BZP	M6	8 mm	8229189
Socket Button	Steel BZP	M6	10 mm	8229183
Socket Button	Steel BZP	M6	50 mm	8229192

Socket Button	Steel BZP	M8	10 mm	8229195
Socket Button	Steel BZP	M8	30 mm	8229199
Socket Button	Steel BZP	M8	35 mm	8229209
Socket Button	Steel BZP	M8	40 mm	8229202
Socket Button	Steel BZP	M8	45 mm	8229206
Socket Button	Steel BZP	M8	50 mm	8229215
Socket Button	Steel BZP	M10	16 mm	8229218
Socket Button	Steel BZP	M10	20 mm	8229212
Socket Button	Steel BZP	M10	25 mm	8229221
Socket Button	Steel BZP	M10	30 mm	8229224
Socket Button	Steel BZP	M10	35 mm	8229228
Socket Button	Steel BZP	M10	40 mm	8229237
Socket Button	Steel BZP	M10	50 mm	8229320

Please view our full range listing below for all BZP Steel Hexagon Socket Button Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Socket Button	Steel BZP	M12	20 mm	8229234
Socket Button	Steel BZP	M12	25 mm	8229243
Socket Button	Steel BZP	M12	30 mm	8229246
Socket Button	Steel BZP	M12	35 mm	8229240
Socket Button	Steel BZP	M12	40 mm	8229259



Thread Size d1		M3	M4	M5	M6	M8	M10	M12	M16
Thread Pitch		0.5	0.7	0.8	1	1.25	1.5	1.75	2
~ISO 7380 Head Dia. d2	min.	5.4	7.24	9.14	10.07	13.57	17.07	20.48	27.48
	max.	5.7	7.60	9.50	10.50	14.00	17.50	21.00	28.00
ANSI B 18.3.4M Head Dia. d2	min.	5.4	7.24	9.14	10.07	13.57	17.07	20.48	27.48
	max.	5.7	7.60	9.50	10.50	14.00	17.50	21.00	28.00
~ISO 7380 Head Height k	min.	1.40	1.95	2.50	3.00	4.10	5.20	6.24	8.44
	max.	1.65	2.20	2.75	3.30	4.40	5.50	6.60	8.80
ANSI B 18.3.4M Head Height k	min.	1.43	1.95	2.50	3.00	4.05	5.20	6.24	8.44
	max.	1.65	2.20	2.75	3.30	4.40	5.50	6.60	8.80
~ISO 7380 Key Size s	Nominal Size	2	2.5	3	4	5	6	8	10
	min.	2.020	2.52	3.020	4.020	5.020	6.020	8.025	10.025
	max.	2.045	2.56	3.071	4.084	5.084	6.095	8.115	10.115
ANSI B 18.3.4M Key Size s	Nominal Size	2	2.5	3	4	5	6	8	10
	min.	2.020	2.52	3.020	4.020	5.020	6.020	8.025	10.025
	max.	2.045	2.56	3.071	4.084	5.084	6.095	8.115	10.115
~ISO 7380 Key Engagement t	min.	1.04	1.3	1.56	2.08	2.60	3.12	4.16	5.20
ANSI B 18.3.4M Key Engagement t	min.	1.04	1.3	1.56	2.08	2.60	3.12	4.16	5.20

Nominal Length	~ ISO 7380		Length Tolerance								ANSI B 18.3.4M	
	min	max	M3	M4	M5	M6	M8	M10	M12	M16	min	max
6	5.76	6.24									5.7	6.3
8	7.71	8.29									7.7	8.3
10	9.71	10.29									9.7	10.3
12	11.65	12.35									11.7	12.3
16	15.65	16.35									15.7	16.3
20	19.58	20.42									19.5	20.5
25	24.58	25.42									24.5	25.5
30	29.58	30.42									29.5	30.5
35	34.5	35.5									34.5	35.5
40	39.5	40.5									39.5	40.5
45	44.5	45.5									44.5	45.5
50	49.5	50.5									49.5	50.5
55	54.4	55.6									54.5	55.5
60	59.4	60.6									59.5	60.5

Nominal Lengths above the stepped line Full Thread

Nominal Lengths below the stepped line, the thread length at the discretion of the manufacturer, may be between a minimum of 2d+12mm and a maximum which is within 2 P of the head.

~ISO 7380	Neither standard is intended for high strength applications. The only purpose of having them produced in property class 10.9 or 12.9 is to increase the wear resistance of the socket drive.
ANSI B 18.3.4M	

~ISO 7380		ANSI B 18.3.4M	
Material	Steel	Stainless Steel	Material
Property Class	10.9	A2 & A4	Property Class
Finish	Furnace Black	Plain	Finish
Thread Tolerance	6g	6g	Thread Tolerance

For More Detailed Information, Please Refer To Complete ISO Or ANSI Standard, Which Are The Governing Standards.

