



0010179


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com




Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010179	N/A	Black

Dimensions	Uncoated		Coated Limits			Packaging
	(mm)	(in)	(mm)	(in)		
OD (A)	16.05	0.632	16.25	0.640	MAX	Box Qty= 340 pcs
ID (C)	9.10	0.359	8.52	0.336	MIN	
HT (B)	28.20	1.111	29.52	1.163	MAX	

Electrical Characteristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x0.5TSx120mm)			Initial Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@100Mhz	200Ω	50%							

The Limit of Breakage					Temperature Rating		
Winding Length Per Turn		Wound Coil Dimensions (mm)			Curie Temp: -30°C-110°C		
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	Coating Temp (Continuous up to): 180°C
					HT	-	
				Completely Full Window	Max OD	-	Notes:
					Max HT	-	
				Surface Area (mm ²)			
				Unwound Core	-		
				40% Winding Factor	-		

IMPEDANCE V.S FREQUENCY



Revision 10/8/2025

