


Technical Requirements:

- 1,100% continuity testing shall be performed on finished products: no short circuit, open circuit or misconnection is allowed.
- 2,Continuity resistance: 2Ω MAX
- 3,Insulation resistance: 10Ω MIN
- 4,Test voltage: 300VDC
- 5,Products comply with ROHS + REACH standards.

P2
Plating Sn

P1
HY2.0-6Y

3.0±0.3mm	Plating Sn	P1	Red
3.0±0.3mm	Plating Sn	P2	White
3.0±0.3mm	Plating Sn	P2	Yellow
3.0±0.3mm	Plating Sn	P2	Green
3.0±0.3mm	Plating Sn	P2	Blue
3.0±0.3mm	Plating Sn	P2	Black

Part		HY2.0-6Y/ plating Sn UL1007-26# L=200mm					
6							
5							
4							
3	Terminal	HY2.0 Plating Sn				6	pcs
2	Housing	HY2.0-6Y White				1	pcs
1	Wire	UL1007-26AWG R/B wire L=200mm,end plating Sn 3mm	103mm	1.0/3.0T		6	pcs
No.	Material	Description	Cut length of the wires	Set wire stripping length	wire length	QTY	Unit



贝迅泽技术（东莞）有限公司
BEIXUNZE TECHNOLOGY (DONGGUAN) CO., LTD

www.hiemi.cn		PN:	HY2.0-6P-A-200-26A	
Drawn	CHC	Date	2024-11-19	A0
Check	LIKE	Date	2024-11-19	
Approved	WSR	Date	2024-11-19	