



# RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2023.11.25



### SPECIFICATIONS

1. Current rating: 3A AC, DC
2. Temperature range: -25°C ~ +85°C
3. Insulation Resistance: 1000MΩ Min.
4. Withstanding voltage: 1000V AC/ minute.
5. Contact Resistance: 10mΩ Max.

### Material:



Insulator: PA66 UL 94V-0 (2)  
 Pin Material: Phosphor Bronze or Brass  
 Plating: Tin plated  
 Poles: 02-15P

### Ordering Code:

B2501R-XX-N0  
 1 2

1. 序列号

2. Pin位数: (02-15)



PIN	尺寸 (mm)	
	A	B
02	2.50	7.50
03	5.00	10.00
04	7.50	12.50
05	10.00	15.00
06	12.50	17.50
07	15.00	20.00
08	17.50	22.50
09	20.00	25.00
10	22.50	27.50
11	25.00	30.00
12	27.50	32.50
13	30.00	35.00
14	32.50	37.50
15	35.00	40.00

X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: B2501R-XX-N0

TITLE: 2.50mm Crimp Style Connectors

APPD: Chen ZhiQiang

CHKD: Liu Wei

DRAW: Chen HongJiang

DATE: 2024.07.27

**XFCN** 兴飞连接器

0769-82001899

www.xfconn.com

DWG NO: /

VIEW:

SCALE: NONE

SHEET: 1/1

REV: A1

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN