



0010888


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com



Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010888	N/A	No

Dimensions	Uncoated		Coated Limits			Packaging
	(mm)	(in)	(mm)	(in)		
OD (A)	27.85	1.097	30.64	1.207	MAX	Box Qty=80 pcs
ID (C)	18.30	0.721	16.84	0.663	MIN	
HT (B)	28.54	1.124	29.68	1.169	MAX	

Electrical Characteristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.65x1TSx120mm)			Initial Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
@25Mhz	110Ω	26°C	1200	360 (1.6kA/m)	140	20.0	5.1	NZO	49.5
@100Mhz	150Ω	50%							

The Limit of Breakage					Temperature Rating		
Winding Length Per Turn			Wound Coil Dimensions (mm)		Curie Temp: >160°C		
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	
				HT	-		
-	-	-	-	Completely Full Window	Max OD	-	
-	-	-	-		Max HT	-	
				Surface Area (mm ²)		Notes:	
				Unwound Core			-
				40% Winding Factor			-

IMPEDANCE V.S FREQUENCY

