



0040613


Jingweitang Industrial Zone,
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: yufengciye@126.com



Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0040613	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging Box Qty=156 pcs
	(mm)	(in)	(mm)	(in)		
OD (A)	36.02	1.419	37.10	1.462	MAX	
ID (C)	21.13	0.833	20.07	0.791	MIN	
HT (B)	10.55	0.416	11.18	0.441	MAX	

Electrical Characteristics			Physical Characteristics						
IMPEDANCE RESULT (Testing Condition:0.55x0.5TSx120mm)			Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	AL(nH/T ²)
			@25Mhz	45Ω	26°C	400	420 (4kA/m)	200	45.0
@100Mhz	90Ω	50%							

WATT LOSS					Temperature Rating		
Winding Length Per Turn				Wound Coil Dimensions (mm)			Curie Temp: >250°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	-	Coating Temp (Continuous up to): 180°C
					HT	-	
-	-	-	-	Completely Full Window	Max OD	-	Notes:
-	-	-	-		Max HT	-	
-	-	-	-	Surface Area (mm ²)			
-	-	-	-	Unwound Core	-		
-	-	-	-	40% Winding Factor	-		

IMPEDANCE V.S FREQUENCY

