







# RoHS

REV	ECN NO.	DESCRIPTION	DESIGN	APPROVAL	DATE
A1	NEW	更换图框			2024.04.17



**NOTES;**

- material: Contact: Steel 304  
body: PA 94-V0;  
over: PC 94-V0;
- removed burrs and sharp edge.
- For ANF, ANG, ANS fuse.
- Suitable rated current: 58VDC 200A.
- RoHS COMPLIANT.
- The fuse holder is capable of functioning individually or in multiple sets;
- Mounting torque: 4.5Nm



X.±0.50	X.°±
.X±0.25	.X°±
.XX±0.15	.XX°±
.XXX±0.10	.XXX°±
UNITS:	mm

PART NO: ANS-H		<b>XFCN</b> 兴飞连接器		
TITLE: 螺栓式汽车保险丝座 2P 黑色		0769-82001899		
		www.xfconn.com		
DWG NO:		/		
APPD		VIEW		
CHKD		SCALE	SHEET	REV
DRAW	Wang	NONE	NO	A1
DATE	2024.04.25			

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF XFCN AND SHALL NOT BE REPRODUCED, COPIED OR CUED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF XFCN