



YUFENGCIYE

**0010889**


Jingweitang Industrial Zone,  
Dalingshan Town, Dongguan City

Sales: Ms. Wang

Mobile number : +86 189-4861-7861

Web: [Http://www.yufengciye.com](http://www.yufengciye.com)

E-mail: [yufengciye@126.com](mailto:yufengciye@126.com)



Product Category	Core Marking			Coating Color
	Lot Number	Part Number	Inductance Grade	
Ferrite Core	2601	0010889	N/A	Green

Dimensions	Uncoated		Coated Limits			Packaging
	(mm)	(in)	(mm)	(in)		
OD (A)	39.05	1.539	39.00	1.537	MAX	Box Qty=48 pcs
ID (C)	18.05	0.711	18.00	0.709	MIN	
HT (B)	9.05	0.357	9.00	0.355	MAX	

Electrical Characteristics			Physical Characteristics						
<b>IMPEDANCE RESULT</b> (Testing Condition:0.65x0.5TSx120mm)			Initial Permeability	Saturation Magnetic Flux Density	Remanence	Coercivity	Density	Material	Weight (g)
			@25Mhz	55Ω	26°C	900	320 (4kA/m)	140	20.0
@100Mhz	95Ω	50%							

The Limit of Breakage					Temperature Rating	
Winding Length Per Turn			Wound Coil Dimensions (mm)			Curie Temp: -30°C-110°C
Winding Factor	(mm)	Winding Factor	(mm)	40% Winding Factor	OD	Coating Temp (Continuous up to): 180°C
					HT	
-	-	-	-	Completely Full Window	Max OD	Notes:
-	-	-	-		Max HT	
				Surface Area (mm <sup>2</sup> )		
				Unwound Core	-	
				40% Winding Factor	-	

**IMPEDANCE V.S FREQUENCY**

